

## IE-SW-PL16MT-14TX-2SC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



Weidmüller's Premium Line consists of high-end switches with advanced management and security features. It is suitable for demanding network solutions. The equipment can be delivered with Fast Ethernet or Gigabit Ethernet ports. With their advanced ring redundancy technology (recovery time  $\leq 20$  ms), these devices raise the reliability and availability of your industrial networks. The optional SFP transceiver can be fitted offering a high degree of flexibility. Gigabit versions permit use in networks with a high volume of communications

- Managed Fast Ethernet versions in a high-quality metal housing (IP 30)
- Versions with 10 or 18 ports and Gigabit uplink ports
- Full Gigabit switch with 9 ports
- Supports all standard TCP/IP-based protocols in industrial networks (for example Ethernet/IP, Modbus/TCP)
- Integrated redundancy mechanisms (recovery time  $\leq 20$  ms) increase the reliability in network ring structures
- Approvals: CE, FCC, cULus, Class I Div. 2 / ATEX, DNV / GL

### General ordering data

Version	Network switch, managed, Fast Ethernet, Number of ports: 14x RJ45, 2x SC Multi-mode, IP30, -40 °C...75 °C
Order No.	<a href="#">1286830000</a>
Type	IE-SW-PL16MT-14TX-2SC
GTIN (EAN)	4050118077582
Qty.	1 pc(s).

## IE-SW-PL16MT-14TX-2SC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	142.7 mm	Depth (inches)	5.618 inch
Height	135 mm	Height (inches)	5.315 inch
Width	94 mm	Width (inches)	3.701 inch
Net weight	1,586 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 Ghz: 10 V/m, IEC 61000-4-4 EFT: Power: 1 kV; Signal: 0,5 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 1 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA nC IIC T4 Gc
Free fall	According to IEC 60068-2-32	Safety standard	UL508, UL 60950-1, EN 60950-1
Shock	according to IEC 60068-2-27	Vibration	according to IEC 60068-2-6

## Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

## Fibre optic transceiver characteristics

Transmission rate	100 Mbps		
Transceiver type	Multimode		
Connector type	SC-Duplex		
Transmission distance, typ.	5 km		
Wavelength	typ.	1,300 nm	
	Wavelength	TX	
	min.	1,260 nm	
	max.	1,360 nm	
	Wavelength	RX	
	min.	1,100 nm	
Receive power	min.	-32 dBm	
	max.	-3 dBm	

Creation date January 22, 2022 9:00:01 AM CET

**IE-SW-PL16MT-14TX-2SC**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data**

Transmission power	min.	-20 dBm
	max.	-10 dBm
Link-budget	12 dB	

**Guarantee**

Time interval	5 years
---------------	---------

**Interfaces**

Alarm contact	2 relay outputs with a current capacity of 1 A at 24 V DC	Console port interface	RS-232
Digital inputs	2 inputs with the same ground, isolated <ul style="list-style-type: none"> <li>+13 To +30 V for logic "1"</li> <li>-30 To +3 V for logic "0"</li> <li>Max. input current: 8 mA</li> </ul>	Fibre-optic ports	100BaseFX ports (SC connector), Multimode
LED indicator	PWR1, PWR2, FAULT, MSTR/HEAD, CPLR/TAIL, 10/100M (TP-Port), 100M (fibre-optic port).	Number of ports	14x RJ45, 2x SC Multimode
RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port		

**MTBF**

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	247,000 h

## IE-SW-PL16MT-14TX-2SC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Management features

Device configuration	Webbrowser (HTTP/HTTPS), SNMP v1/v2c/v3, Telnet console, Local serial console port (RS-232 via RJ-45 port), Windows tool	Monitoring function	SNMP v1/v2c/v3, Link Layer Discovery Protocol (LLDP), Port mirroring, Port statistics, Port monitoring, Syslog, RMON (Remote monitoring), Event based warning via E-Mail, Event based warning via relay, Event based warning via SNMP trap
Network redundancy	Spanning Tree Protocol (STP), Rapid Spanning Tree Protocol (RSTP), Turbo-Ring (recovery time <20 ms), Turbo-Chain (recovery time <20 ms), Link Aggregation Control Protocol (LACP)	Network traffic filter	Quality of Service (QoS), Tag based VLAN, Port based VLAN, IGMP v1/v2, GMRP, Traffic Rate Limiting
IP-address management	Static, BootP, RARP, DHCP-Client, DHCP-Server (port based), DHCP Option 82 (Relay Agent)	Security functions	VLAN segmentation, Enable/disable ports, Access control (port based via IEEE 802.1X), Access control list (MAC-based), Loop protection, TACACS + and IEEE 802.1X User Authentication
Time synchronization management	SNTP client, NTP client, PTPv1	Industrial protocol support	PROFINET device acc. to conformance class B, EtherNet/IP, Modbus/TCP slave

## Power supply

Connection type	2 removable 6-pin terminal blocks		
Current consumption	Voltage	24 V DC	
	Current	0.51 A	
Overload current protection	Existing		
Reverse polarity protection	Yes		
Voltage supply	12/24/48 V DC, 2 redundant inputs		
Voltage supply range	Voltage type	DC	
	Voltage, min.	12 V	
	Voltage, max.	45 V	

## Switch characteristics

Bandwidth backplane	3.2 Gbps	IGMP-Groups	256
MAC table size	8 K	Max. number of available VLANs	64
Packet buffer size	2 Mbit	Priority queues	4
VLAN-ID max	4,094	VLAN-ID min	1

## Technical data

Housing main material	metal	Protection degree	IP30
Speed	Fast Ethernet	Switch	managed
Type of mounting	DIN rail, Panel (with optional mounting kit)		

Creation date January 22, 2022 9:00:01 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

4

## IE-SW-PL16MT-14TX-2SC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
MIB	MIB-II, Ethernet-Like MIB, P-BRIDGE MIB, Q-BRIDGE MIB, Bridge MIB, RSTP MIB, RMON MIB Group 1, 2, 3, 9	Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3x for flow control, IEEE 802.1D-2004 for the Spanning Tree protocol, IEEE 802.1w for Rapid STP, IEEE 802.1Q for VLAN tagging, IEEE 802.1p for Class of Service, IEEE 802.1X for authentication, IEEE 802.3ad for port trunk with LACP

## Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ECLASS 9.0	19-17-01-06
ECLASS 9.1	19-17-01-06	ECLASS 10.0	19-17-04-01
ECLASS 11.0	19-17-04-01		

## Approvals

Approvals



ROHS	Conform
UL File Number Search	E230683

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">ODVA Certificate</a> <a href="#">DNV-GL certificate</a> <a href="#">ATEX certificate</a> <a href="#">EU Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Product Change Notification	<a href="#">Firmware Release Notes</a>
Software	<a href="#">Device description – SNMP MIB file</a> <a href="#">Device description – GSDML IE-SW-PL16M-series</a> <a href="#">Device description – EDS IE-SW-PL16M-series</a> <a href="#">Software unit – Managed Switch Configuration Utility</a> <a href="#">Firmware – Firmware Version 3.4.18</a>
User Documentation	<a href="#">Hardware Installation Guide</a> <a href="#">Manual</a> <a href="#">20191204 Security Advisory IE Managed Switches</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

Creation date January 22, 2022 9:00:01 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

5

## IE-SW-PL16MT-14TX-2SC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

# Accessories

## Mounting kit for 19" rack assembly


- For assembling DIN rail-based devices on 19" racks



### General ordering data

Type	RM-KIT	Version
Order No.	<a href="#">1241440000</a>	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	

## Mounting kit for wall mounting



Mounting kit for alternative wall-mounting of DIN rail-based (top-hat type) Industrial Ethernet components.

**IE-WALLMOUNT-KIT-30MM** for use with:

- Industrial Ethernet Switches of the product range **IE-SW-BL05**

**IE-WALLMOUNT-KIT-46MM** for use with:

- Industrial Ethernet Switches of the product ranges **IE-SW- BL06/BL08/VL05/VL08/VL09/VL16/PL06/PL08/PL09/PL10/PL16/PL18**
- Industrial Ethernet media converters of the product range **IE-MC-VL**
- Industrial Ethernet switches of the product range **IE-WL-AP**

### General ordering data

Type	IE-WALLMOUNT-KIT-46MM
Order No.	<a href="#">1504440000</a>
GTIN (EAN)	4050118312317
Qty.	1 pc(s).

**IE-SW-PL16MT-14TX-2SC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories****Configuration backup and restore module (for use with switches of Value- and PremiumLine such as Basic- and ValueLine WLAN devices)****Module for saving and loading a device configuration**

- Reduced system downtime by simple reconfiguration if equipment is swapped over
- Automatic loading of the saved configuration possible after device restart
- Compact and robust design
- Useable with all Weidmüller managed switches and industrial WLAN devices

**General ordering data**

Type	EBR-MODULE RS232	Version
Order No.	<a href="#">1241430000</a>	Configuration module, IP40, 0 °C...60 °C
GTIN (EAN)	4050118029086	
Qty.	1 pc(s).	

**Ethernet (Cat.6)**

- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

**General ordering data**

Type	VDATE CAT6	Version
Order No.	<a href="#">1348590000</a>	Terminal rail fixing, Surge protection, Cat.6, 802.3 at Type 1, 802.3 at Type 2, 802.3 bt Type 3, U <sub>p</sub> (L/N-PE) ≤ 550 V
GTIN (EAN)	4050118153002	
Qty.	1 pc(s).	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1286830000](#)