

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image



- Wide ranges of variations with 5 to 16 ports
- Variations for Gigabit Ethernet
- Two redundant power inputs 12/24/48 V DC
- Models with copper and fibre-optic interface (multimode and singlemode)
- Extensive approvals: CE, FCC, cULus, Class I Div. 2 / ATEX Zone 2, DNV-GL

General ordering data

Version	Network switch, unmanaged, Gigabit Ethernet, Number of ports: 6 * RJ45 10/100/1000BaseT(X), 2 * combo-ports (10/100/1000BaseT(X) or 100/1000BaseSFP), IP30, -40 °C...75 °C
Order No.	1286870000
Type	IE-SW-VL08T-6GT-2GS
GTIN (EAN)	4050118077759
Qty.	1 pc(s).

Creation date January 22, 2022 9:37:14 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	105 mm	Depth (inches)	4.134 inch
Height	135 mm	Height (inches)	5.315 inch
Width	52.85 mm	Width (inches)	2.081 inch
Net weight	630 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 Ghz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 2 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA nC IIC T4 Gc
Free fall	According to IEC 60068-2-32	Safety standard	UL508, EN 60950-1
Ship use	DNV-GL	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Guarantee

Time interval	5 years
---------------	---------

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Interfaces

Alarm contact	1 relay output with a current capacity of 1 A at 24 V DC	Fibre-optic ports	100/1000Base SFP Slot
Function DIP switch	Port surveillance, Broadcast storm protection enable/disable, Enable/disable jumbo frame support, Activate/deactivate IEEE 802.3az energy-efficient Ethernet	LED indicator	Power LED: PWR1, PWR2, FAULT, 10/100/1000M (TP-Port), 100/1000M (SFP-Port)
Note	The SFP slot can only be used with Weidmüller SFP transceivers. Third-party SFP transceivers are not accepted by the switch.	Number of ports	6 * RJ45 10/100/1000BaseT(X), 2 * combo-ports (10/100/1000BaseT(X) or 100/1000BaseSFP)
RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port		

MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	2,283,188 h

Power supply

Connection type	1 removable 6-pin terminal block		
Current consumption	0.34 A at 24 V		
Reverse polarity protection	Available		
Voltage supply	12/24/48 V DC, 2 redundant inputs		
Voltage supply range	Voltage type	DC	
	Voltage, min.	9.6 V	
	Voltage, max.	60 V	

Switch characteristics

Bandwidth backplane	16 Gbps	Jumbo frame support	up to 9.6 KB
MAC table size	8 K	Packet buffer size	4,000 Kbit

Technical data

Housing main material	Metal	Protection degree	IP30
Speed	Gigabit Ethernet	Switch	unmanaged
Type of mounting	DIN rail, Panel (with optional mounting kit)		

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3ab for 1000BaseT(X), IEEE 802.3z for 1000BaseX, IEEE 802.3x for flow control, IEEE 802.3az Energy-Efficient Ethernet		

Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ECLASS 9.0	19-17-01-06
ECLASS 9.1	19-17-01-06	ECLASS 10.0	19-17-04-02
ECLASS 11.0	19-17-04-02		

Approvals

Approvals



ROHS	Conform
UL File Number Search	E141197

Downloads

Approval/Certificate/Document of Conformity	CC-Link IE Field Certificate DNV-GL certificate ATEX certificate EU Declaration of Conformity
Engineering Data	CAD data – STEP
Product Change Notification	Product Change Notification IE-SW-VL08-GT-series
User Documentation	Hardware Installation Guide
Catalogues	Catalogues in PDF-format
Brochures	

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Mounting kit for 19" rack assembly


- For assembling DIN rail-based devices on 19" racks



General ordering data

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	

Mounting kit for wall mounting



Mounting kit for alternative wall-mounting of DIN rail-based (top-hat type) Industrial Ethernet components.

IE-WALLMOUNT-KIT-30MM for use with:

- Industrial Ethernet Switches of the product range **IE-SW-BL05**

IE-WALLMOUNT-KIT-46MM for use with:

- Industrial Ethernet Switches of the product ranges **IE-SW- BL06/BL08/VL05/VL08/VL09/VL16/PL06/PL08/PL09/PL10/PL16/PL18**
- Industrial Ethernet media converters of the product range **IE-MC-VL**
- Industrial Ethernet switches of the product range **IE-WL-AP**

General ordering data

Type	IE-WALLMOUNT-KIT-46MM
Order No.	1504440000
GTIN (EAN)	4050118312317
Qty.	1 pc(s).

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

SFP transceiver (for use with switches of Basic-, Value- and PremiumLine)



- Supports DDM (Digital Diagnostic Monitoring)
- IEEE 802.3z compliant (Gigabit Ethernet SFPs)
- IEEE 802.3u compliant (Fast Ethernet SFPs)
- Symmetric LVPECL I/Os (Gigabit Ethernet SFPs)
- Symmetric PECL I/Os (Fast Ethernet SFPs)
- TTL signal detection indicator
- Pluggable in operation (hot pluggable)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Basic-, Value- and PremiumLine

General ordering data

Type	IE-SFP-1G10ALC	
Order No.	1241530000	
GTIN (EAN)	4050118029406	
Qty.	1 pc(s).	
Type	IE-SFP-1G10ALC-T	
Order No.	1286740000	
GTIN (EAN)	4050118077735	
Qty.	1 pc(s).	
Type	IE-SFP-1GLSXLC-T	Version
Order No.	1286710000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 2 km, -40 °C...85
GTIN (EAN)	4050118077520	°C
Qty.	1 pc(s).	
Type	IE-SFP-1G10BLC	
Order No.	1241540000	
GTIN (EAN)	4050118029376	
Qty.	1 pc(s).	
Type	IE-SFP-1GLXLC-T	Version
Order No.	1286720000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 10 km, -40
GTIN (EAN)	4050118077537	°C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1G20BLC	
Order No.	1241570000	
GTIN (EAN)	4050118029383	
Qty.	1 pc(s).	
Type	IE-SFP-1GSXLC	Version
Order No.	1241490000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 0.55 km, 0
GTIN (EAN)	4050118029512	°C...60 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GSXLC-T	Version
Order No.	1286700000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 0.55 km, -40
GTIN (EAN)	4050118077261	°C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GLSXLC	Version
Order No.	1241500000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 2 km, 0 °C...60
GTIN (EAN)	4050118029314	°C
Qty.	1 pc(s).	
Type	IE-SFP-1GLXLC	Version
Order No.	1241510000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 10 km, 0
GTIN (EAN)	4050118029338	°C...60 °C
Qty.	1 pc(s).	

Creation date January 22, 2022 9:37:14 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	IE-SFP-1GLHXLC-T	Version
Order No.	1286730000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, -40
GTIN (EAN)	4050118077728	°C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1FEMLC-T	Version
Order No.	1241450000	SFP Transceiver, 100 Mbps, Multimode, LC-Duplex, 4 km, -40 °C...85
GTIN (EAN)	4050118029192	°C
Qty.	1 pc(s).	
Type	IE-SFP-1G20ALC	
Order No.	1241550000	
GTIN (EAN)	4050118029505	
Qty.	1 pc(s).	
Type	IE-SFP-1G10BLC-T	
Order No.	1286750000	
GTIN (EAN)	4050118077544	
Qty.	1 pc(s).	
Type	IE-SFP-1G20ALC-T	
Order No.	1286760000	
GTIN (EAN)	4050118077278	
Qty.	1 pc(s).	
Type	IE-SFP-1G20BLC-T	
Order No.	1286770000	
GTIN (EAN)	4050118077513	
Qty.	1 pc(s).	
Type	IE-SFP-1FESLC-T	Version
Order No.	1241470000	SFP Transceiver, 100 Mbps, Singlemode, LC-Duplex, 40 km, -40
GTIN (EAN)	4050118029420	°C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GLHXLC	Version
Order No.	1241520000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, 0
GTIN (EAN)	4050118029369	°C...60 °C
Qty.	1 pc(s).	
Type	IE-SFP-1FELLC-T	Version
Order No.	1241480000	SFP Transceiver, 100 Mbps, Singlemode, LC-Duplex, 80 km, -40
GTIN (EAN)	4050118029178	°C...85 °C
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1286870000](#)