

**CC-M 30/60 2X3 AL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	MetalliCard, Device markers, 30 x 60 mm, silver
Order No.	<a href="#">1327850000</a>
Type	CC-M 30/60 2X3 AL
GTIN (EAN)	4050118132700
Qty.	100 pc(s).

## CC-M 30/60 2X3 AL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.02 inch
Height	30 mm	Height (inches)	1.181 inch
Width	60 mm	Width (inches)	2.362 inch
Net weight	2.2 g		

### Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

### General data

Colour	silver	Material	Chrome coated aluminium (AL)
Number of markers per combination	1 MetalliCard = Device markers	Operating temperature range	-55...130 °C
Operating temperature range, max.	130 °C	Operating temperature range, min.	-55 °C
Recommended industries	Energy, Process	Size of labelling field	30.2 x 57.2 mm
Width	60 mm		

### Device markers

Drill-hole diameter	3.3 mm
---------------------	--------

### Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04		

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**


**CC-M 30/60 2X3 AL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Example of use**



## CC-M 30/60 2X3 AL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Complementary products



### General ordering data

Type	INLAY CC-M UNIVERSAL
Order No.	<a href="#">1341120000</a>
GTIN (EAN)	4050118145458
Qty.	1 pc(s).

Type	INLAY CC-M 30/60
Order No.	<a href="#">1341070000</a>
GTIN (EAN)	4050118145502
Qty.	1 pc(s).

Type	PRIMER CC-M
Order No.	<a href="#">2068020000</a>
GTIN (EAN)	4050118416534
Qty.	100 pc(s).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1327850000](#)