

## SLF 5.08/02/180FI SN OR BX

**Weidmüller Interface GmbH & Co. KG**



Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

### Product image



Male plug with PUSH IN wire connection and straight outlet direction, when used with BLF 5.08HC as wire-to-wire application for panel feed-through. The male plugs provide space for labelling and can be coded.

### General ordering data

|              |  |
|--------------|--|
| Version      | PCB plug-in connector, male plug, 5.08 mm,<br>Number of poles: 2, 180°, PUSH IN with actuator,<br>Tension-clamp connection, Clamping range, max. :<br>3.31 mm <sup>2</sup> , Box |
| Order No.    | <a href="#">1336400000</a>   |
| Type         | SLF 5.08/02/180FI SN OR BX   |
| GTIN (EAN)   | 4050118140293  |
| Qty.         | 90 pc(s).  |
| Product data | IEC: 400 V / 25.9 A / 0.2 - 2.5 mm <sup>2</sup><br>UL: 300 V / 14 A / AWG 26 - AWG 12  |
| Packaging    | Box  |

Creation date January 23, 2022 3:23:45 PM CET

## SLF 5.08/02/180FI SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 30 mm   | Depth (inches)  | 1.181 inch |
| Height     | 14.2 mm | Height (inches) | 0.559 inch |
| Net weight | 4.703 g |                 |            |

## System Parameters

|  |  |                   |                             |
|--|--|-------------------|-----------------------------|
| Product family                               | OMNIMATE Signal - series BL/SL 5.08              |                   |                             |
| Type of connection                           | Field connection                                 |                   |                             |
| Wire connection method                       | PUSH IN with actuator, Tension-clamp connection  |                   |                             |
| Pitch in mm (P)                              | 5.08 mm  |                   |                             |
| Pitch in inches (P)                          | 0.2 inch   |                   |                             |
| Conductor outlet direction                   | 180°   |                   |                             |
| Number of poles                              | 2  |                   |                             |
| L1 in mm                                     | 5.08 mm  |                   |                             |
| L1 in inches                                 | 0.2 inch   |                   |                             |
| Pin series quantity                          | 1  |                   |                             |
| Rated cross-section                          | 2.5 mm <sup>2</sup>                              |                   |                             |
| Touch-safe protection acc. to DIN VDE 57 106 | finger-safe plugged/ back-of-hand-safe unplugged |                   |                             |
| Protection degree                            | IP20   |                   |                             |
| Volume resistance                            | 4.50 mΩ  |                   |                             |
| Can be coded                                 | Yes  |                   |                             |
| Stripping length                             | 10 mm  |                   |                             |
| Screwdriver blade                            | 0.6 x 3.5  |                   |                             |
| Screwdriver blade standard                   | DIN 5264   |                   |                             |
| Plugging cycles                              | 25   |                   |                             |
| Plugging force/pole, max.                    | 7 N  |                   |                             |
| Pulling force/pole, max.                     | 5.5 N  |                   |                             |
| Tightening torque                            | Torque type                                      | Screw flange      |                             |
|  | Usage information                                | Tightening torque | min. 0.2 Nm<br>max. 0.25 Nm |

## Material data

|                                       |                            |                                       |        |
|---------------------------------------|----------------------------|---------------------------------------|--------|
| Insulating material                   | PBT                        | Colour                                | orange |
| Colour chart (similar)                | RAL 2000                   | UL 94 flammability rating             | V-0    |
| Contact material                      | CuSn                       | Contact surface                       | tinned |
| Layer structure of plug contact       | 4...8 μm Sn hot-dip tinned | Storage temperature, min.             | -40 °C |
| Storage temperature, max.             | 70 °C                      | Operating temperature, min.           | -50 °C |
| Operating temperature, max.           | 100 °C                     | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 100 °C                     |                                       |        |

## Conductors suitable for connection

|   |                      |
|---|----------------------|
| Clamping range, min.                    | 0.13 mm <sup>2</sup> |
| Clamping range, max.                    | 3.31 mm <sup>2</sup> |
| Wire connection cross section AWG, min. | AWG 26               |
| Wire connection cross section AWG, max. | AWG 12               |
| Solid, min. H05(07) V-U                 | 0.2 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U                 | 2.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K              | 0.2 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K              | 2.5 mm <sup>2</sup>  |

Creation date January 23, 2022 3:23:45 PM CET

## SLF 5.08/02/180FI SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm<sup>2</sup>  
 min.

w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm<sup>2</sup>  
 max.

w. wire end ferrule, DIN 46228 pt 1, 0.2 mm<sup>2</sup>  
 min.

w. wire end ferrule, DIN 46228 pt 1, 2.5 mm<sup>2</sup>  
 max.

Plug gauge in accordance with EN 60999 a x b; ø 2.8 mm x 2.0 mm

| Clampable conductor                    | Cross-section for conductor connection | Type                         | fine-wired                   |
|--|--|------------------------------|------------------------------|
|  |  |                              | nominal                      |
| wire end ferrule                       |  | Stripping length             | nominal 12 mm                |
|  |  | Recommended wire-end ferrule | <a href="#">H0.5/16 OR</a>   |
|  |  | Stripping length             | nominal 10 mm                |
|  |  | Recommended wire-end ferrule | <a href="#">H0.5/10</a>      |
| Cross-section for conductor connection | Type                                   | fine-wired                   |                              |
|  | nominal                                | 0.75 mm <sup>2</sup>         |                              |
| wire end ferrule                       |  | Stripping length             | nominal 12 mm                |
|  |  | Recommended wire-end ferrule | <a href="#">H0.75/16 W</a>   |
|  |  | Stripping length             | nominal 10 mm                |
|  |  | Recommended wire-end ferrule | <a href="#">H0.75/10</a>     |
| Cross-section for conductor connection | Type                                   | fine-wired                   |                              |
|  | nominal                                | 1 mm <sup>2</sup>            |                              |
| wire end ferrule                       |  | Stripping length             | nominal 12 mm                |
|  |  | Recommended wire-end ferrule | <a href="#">H1.0/16D R</a>   |
|  |  | Stripping length             | nominal 10 mm                |
|  |  | Recommended wire-end ferrule | <a href="#">H1.0/10</a>      |
| Cross-section for conductor connection | Type                                   | fine-wired                   |                              |
|  | nominal                                | 1.5 mm <sup>2</sup>          |                              |
| wire end ferrule                       |  | Stripping length             | nominal 10 mm                |
|  |  | Recommended wire-end ferrule | <a href="#">H1.5/10</a>      |
|  |  | Stripping length             | nominal 12 mm                |
|  |  | Recommended wire-end ferrule | <a href="#">H1.5/16 R</a>    |
| Cross-section for conductor connection | Type                                   | fine-wired                   |                              |
|  | nominal                                | 2.5 mm <sup>2</sup>          |                              |
| wire end ferrule                       |  | Stripping length             | nominal 10 mm                |
|  |  | Recommended wire-end ferrule | <a href="#">H2.5/14DS BL</a> |

Reference text The outside diameter of the plastic collar should not be larger than the pitch (P). Length of ferrules is to be chosen depending on the product and the rated voltage.

## SLF 5.08/02/180FI SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany


www.weidmueller.com

## Technical data


## Rated data acc. to IEC

|   |                        |   |                   |
|---|------------------------|---|-------------------|
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 25.9 A            |
| Rated current, max. number of poles (Tu=20°C)                             | 21.7 A                 | Rated current, min. number of poles (Tu=40°C)                         | 22.5 A            |
| Rated current, max. number of poles (Tu=40°C)                             | 18.5 A                 | Rated voltage for surge voltage class / pollution degree II/2         | 400 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

## Rated data acc. to CSA

|                                   |   |                                   |                |
|-----------------------------------|---|-----------------------------------|----------------|
| Institute (CSA)                   |  | Certificate No. (CSA)             | 200039-1121690 |
| Rated voltage (Use group B / CSA) | 300 V   | Rated voltage (Use group D / CSA) | 300 V          |
| Rated current (Use group B / CSA) | 10 A  | Rated current (Use group D / CSA) | 10 A           |
| Wire cross-section, AWG, min.     | AWG 26  | Wire cross-section, AWG, max.     | AWG 12         |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate.            |                                   |                |

## Rated data acc. to UL 1059

|                                       |   |                                       |        |
|---------------------------------------|---|---------------------------------------|--------|
| Institute (cURus)                     |  | Certificate No. (cURus)               | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V   | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 14 A  | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 26  | Wire cross-section, AWG, max.         | AWG 12 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate.              |                                       |        |

## Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 352 mm |
| VPE width | 135 mm | VPE height | 38 mm  |

## Type tests

|                              |            |  |
|------------------------------|------------|--|
| Test: Durability of markings | Standard   | IEC 61984 section 6.2 and 7.3.2 / 10.11, IEC 60068-2-70 / 12.95          |
|                              | Test       | mark of origin, type identification, pitch, date clock, type of material |
|                              | Evaluation | available  |
|                              | Test       | durability   |
|                              | Evaluation | passed   |

Creation date January 23, 2022 3:23:45 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

4

## SLF 5.08/02/180FI SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

|  |                |  |                              |  |
|--|----------------|--|------------------------------|--|
| Test: Misengagement (Non-interchangeability) | Standard       | IEC 61984 section 6.3 and 6.9.1 / 10.11, IEC 60512-13-5 / 02.06              |                              |  |
|  | Test           | 180° turned with coding elements   |                              |  |
|  | Evaluation     | passed   |                              |  |
|  | Test           | visual examination   |                              |  |
| Test: Clampable cross section                | Evaluation     | passed   |                              |  |
|  | Standard       | IEC 60999-1 section 7 and 9.1 / 11.99, IEC 60947-1 section 8.2.4.5.1 / 03.11 |                              |  |
|  | Conductor type | Type of conductor and conductor cross-section                                | solid 0.5 mm <sup>2</sup>    |  |
|  |                | Type of conductor and conductor cross-section                                | stranded 0.5 mm <sup>2</sup> |  |
|  |                | Type of conductor and conductor cross-section                                | stranded 1.0 mm <sup>2</sup> |  |
|  |                | Type of conductor and conductor cross-section                                | solid 2.5 mm <sup>2</sup>    |  |
|  |                | Type of conductor and conductor cross-section                                | AWG 26/1                     |  |
|  |                | Type of conductor and conductor cross-section                                | AWG 26/19                    |  |
|  |                | Type of conductor and conductor cross-section                                | AWG 14/1                     |  |
|  |                | Type of conductor and conductor cross-section                                | AWG 14/19                    |  |
| Evaluation                                   | passed         |  |                              |  |

**SLF 5.08/02/180FI SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

|   |                |   |           |
|---|----------------|---|-----------|
| Test for damage to and accidental loosening of conductors | Standard       | IEC 60999-1 section 9.4 / 11.99               |           |
|   | Requirement    | 0.2 kg  |           |
|   | Conductor type | Type of conductor and conductor cross-section | AWG 26/1  |
|   |                | Type of conductor and conductor cross-section | AWG 26/19 |
|   | Evaluation     | passed  |           |
|   | Requirement    | 0.3 kg  |           |
|   | Conductor type | Type of conductor and conductor cross-section | H05V-U0.5 |
|   |                | Type of conductor and conductor cross-section | H05V-K0.5 |
|   | Evaluation     | passed  |           |
|   | Requirement    | 0.7 kg  |           |
|   | Conductor type | Type of conductor and conductor cross-section | H07V-K2.5 |
|   |                | Type of conductor and conductor cross-section | H07V-U2.5 |
| Type of conductor and conductor cross-section             |                | AWG 14/1                                      |           |
| Type of conductor and conductor cross-section             |                | AWG 14/19                                     |           |
| Evaluation  | passed         |   |           |
| Pull-out test   | Standard       | IEC 60999-1 section 9.5 / 11.99               |           |
|   | Requirement    | ≥10 N   |           |
|   | Conductor type | Type of conductor and conductor cross-section | AWG 26/1  |
|   |                | Type of conductor and conductor cross-section | AWG 26/19 |
|   | Evaluation     | passed  |           |
|   | Requirement    | ≥20 N   |           |
|   | Conductor type | Type of conductor and conductor cross-section | H05V-U0.5 |
|   |                | Type of conductor and conductor cross-section | H05V-K0.5 |
|   | Evaluation     | passed  |           |
|   | Requirement    | ≥50 N   |           |
|   | Conductor type | Type of conductor and conductor cross-section | H07V-K2.5 |
|   |                | Type of conductor and conductor cross-section | H07V-U2.5 |
| Type of conductor and conductor cross-section             |                | AWG 14/1                                      |           |
| Type of conductor and conductor cross-section             |                | AWG 14/19                                     |           |
| Evaluation  | passed         |   |           |

## SLF 5.08/02/180FI SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
| ETIM 8.0    | EC002638    | ECLASS 9.0  | 27-44-03-09 |
| ECLASS 9.1  | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-46-02-02 |             |             |

## Important note

|                |   |
|----------------|---|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.  |
| Notes          | <ul style="list-style-type: none"> <li>• Additional colours on request</li> <li>• Gold-plated contact surfaces on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule without plastic collar to DIN 46228/1</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Crimping shape "A" for wire end ferrules with PZ 6/5 crimping tool recommended.</li> <li>• The test point can only be used as potential-pickup point.</li> </ul> |

## Approvals

Approvals



|                       |         |
|-----------------------|---------|
| ROHS                  | Conform |
| UL File Number Search | E60693  |

## Downloads

|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>  |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FLIndustr.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL_BASE STATION EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |

Creation date January 23, 2022 3:23:45 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.


SLF 5.08/02/180FI SN OR BX

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

Drawings


Product image




Dimensional drawing



Graph



Graph



Product benefits



Uncompromising functionality  
 High vibration resistance

Product benefits



Solid PUSH IN contact  
 Safe and durable



**SLF 5.08/02/180FI SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)


**Drawings**

**Product benefits**



Lower assembly costs  
Secure in a matter of seconds

**Product benefits**



Easy handling  
No implementation framework necessary

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1336400000](#)