

IE-SW-BL05T-4TX-1ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

- Variations with 5 or 8 ports
- Variations for Gigabit Ethernet
- Sturdy metal housing
- Compact design
- Two redundant power inputs 12/24/48 V DC
- Variations with copper and fibre-optic interface (multimode and singlemode)
- Extensive approvals: CE, FCC, cULus, Class I Div. 2 / ATEX Zone 2, DNV-GL

General ordering data

Version	Network switch, unmanaged, Fast Ethernet, Number of ports: 4 x RJ45, 1 * ST Multi-mode, IP30, -40 °C...75 °C
Order No.	1286540000
Type	IE-SW-BL05T-4TX-1ST
GTIN (EAN)	4050118076981
Qty.	1 pc(s).

Creation date January 22, 2022 8:49:19 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

IE-SW-BL05T-4TX-1ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	115 mm	Height (inches)	4.528 inch
Width	30 mm	Width (inches)	1.181 inch
Net weight	175 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 Ghz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 1 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA IIC T4 Gc
Free fall	According to IEC 60068-2-32	Safety standard	UL508
Ship use	DNV-GL	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	100 Mbps		
Transceiver type	Multimode		
Connector type	ST-Duplex		
Transmission distance, typ.	5 km		
Wavelength	typ.	1,300 nm	
	Wavelength	TX	
	min.	1,260 nm	
	max.	1,360 nm	
	Wavelength	RX	
	min.	1,100 nm	
	max.	1,600 nm	

Creation date January 22, 2022 8:49:19 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

2

IE-SW-BL05T-4TX-1ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Receive power	min.	-32 dBm
	max.	-3 dBm
Transmission power	min.	-20 dBm
	max.	-10 dBm
Link-budget	12 dB	

Guarantee

Time interval	5 years
---------------	---------

Interfaces

Fibre-optic ports	100BaseFX ports (ST connector), Multimode	Function DIP switch	1x for enabling/disabling the broadcast storm protection
LED indicator	PWR1, PWR2, 10/100M (TP-Port), 100M (fibre-optic port).	Number of ports	4 x RJ45, 1 * ST Multi-mode
RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port		

MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	3,040,784 h

Power supply

Connection type	1 removable 4-pin terminal block		
Current consumption	0.11 A at 24 V		
Overload current protection	1.1 A		
Reverse polarity protection	Available		
Voltage supply	12/24/48 V DC, 2 redundant inputs		
Voltage supply range	Voltage type	DC	
	Voltage, min.	9.6 V	
	Voltage, max.	60 V	

Switch characteristics

Bandwidth backplane	1 Gbps	MAC table size	1 K
Packet buffer size	512 Kbit		

Technical data

Housing main material	Aluminium	Protection degree	IP30
Speed	Fast Ethernet	Switch	unmanaged
Type of mounting	DIN rail, Panel (with optional mounting kit)		

IE-SW-BL05T-4TX-1ST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Technology


Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3x for flow control		

Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ECLASS 9.0	19-17-01-06
ECLASS 9.1	19-17-01-06	ECLASS 10.0	19-17-04-02
ECLASS 11.0	19-17-04-02		

Approvals

Approvals



ROHS	Conform
UL File Number Search	E141197

Downloads

Approval/Certificate/Document of Conformity	DNV-GL certificate ATEX certificate KC certificate EU Declaration of Conformity
Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Product Change Notification	Product Change Notification IE-SW-BL05-series
User Documentation	Hardware Installation Guide
Catalogues	Catalogues in PDF-format

IE-SW-BL05T-4TX-1ST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Mounting kit for 19" rack assembly


- For assembling DIN rail-based devices on 19" racks



General ordering data

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	

Mounting kit for wall mounting



Mounting kit for alternative wall-mounting of DIN rail-based (top-hat type) Industrial Ethernet components.

IE-WALLMOUNT-KIT-30MM for use with:

- Industrial Ethernet Switches of the product range **IE-SW-BL05**

IE-WALLMOUNT-KIT-46MM for use with:

- Industrial Ethernet Switches of the product ranges **IE-SW- BL06/BL08/VL05/VL08/VL09/VL16/PL06/PL08/PL09/PL10/PL16/PL18**
- Industrial Ethernet media converters of the product range **IE-MC-VL**
- Industrial Ethernet switches of the product range **IE-WL-AP**

General ordering data

Type	IE-WALLMOUNT-KIT-30MM
Order No.	1504450000
GTIN (EAN)	4050118312300
Qty.	1 pc(s).

IE-SW-BL05T-4TX-1ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ethernet (Cat.6)



- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

General ordering data

Type	VDATA CAT6	Version
Order No.	1348590000	Terminal rail fixing, Surge protection, Cat.6, 802.3 at Type 1, 802.3 at
GTIN (EAN)	4050118153002	Type 2, 802.3 bt Type 3, U _p (L/N-PE) ≤ 550 V
Qty.	1 pc(s).	

ST



Mounting rail outlet, ST junction design according to IEC 61754-2

General ordering data

Type	IE-XM-ST/ST	Version
Order No.	8808340000	Mounting rail outlet, fibre-optic, ST-ST coupler, IP20
GTIN (EAN)	4032248505920	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1286540000](#)