

RSMS-8 24V+ BASE S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Relay bases (RSM) with common positive and negative to be connected to PLC or other type of controllers. The interfaces are made up of groups of 4, 8 or 16 RCL relays (12.7 mm) or RSS (6.1 mm). The connection to the controller can be set up using pluggable connectors or using direct cabling with IEC 60603-13 connectors. Wide range of options:

- 1 or 2 CO contacts with 16/8/6 A relays
- Voltages from 5 to 230 V
- Screw, tension clamp or PUSH IN connection
- Compatible with Weidmüller's solid-state relays

The range of relays provides galvanic isolation between input/output as well as between the adjacent contacts on the relays. This enables the various voltages in the controllers and those required by the various field elements to be safely adapted.

General ordering data

Version	Interface, RSM, Screw connection
Order No.	1456810000
Type	RSMS-8 24V+ BASE S
GTIN (EAN)	4050118262988
Qty.	1 pc(s).

RSMS-8 24V+ BASE S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	85 mm	Depth (inches)	3.346 inch
Height	109 mm	Height (inches)	4.291 inch
Width	61 mm	Width (inches)	2.402 inch
Net weight	173 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Rated data UL

Operating temperature UL, max.	50 °C	Operating temperature UL, min.	0 °C
Rated current I_N	7.1 A	Rated voltage DC U_N (supply)	24 V DC \pm 10%
Rated current (supply)	2.6 A	Rated voltage DC U_N (input)	24 V DC \pm 10%
Rated voltage AC U_N (output)	250 V AC	Rated current I_{max} (output)	4.5 A

General data

LED status display per relay	green	LED status of the supply voltage	yellow
------------------------------	-------	----------------------------------	--------

Connection data

Connection (field side)	LL3R 5.08 mm	Connection on control side	LP 5.08 mm, LL 5.08 mm
-------------------------	--------------	----------------------------	------------------------

Rating data

Mechanical service life	5 x 10 ⁶ switching cycles
-------------------------	--------------------------------------

Ratings data input

Input voltage	24 V DC \pm 10%	Input current	7.1 mA
---------------	-------------------	---------------	--------

Ratings data output

Relay type	RSS	Type of output	Potential-free contact
Rated voltage	\leq 250 V AC	Max. AC continuous current	4.5 A
Minimum contact current	100 mA	Minimum contact voltage	5 V

Insulation coordination (EN50178)

Pollution severity level	2	Pulse voltage test (1,2/50 μ s)	6 kV
Insulation test voltage	1.2 kVAC		

Insulation coordinates (EN50178)

Rated input insulation voltage	< 50 V AC	Rated output insulation voltage	250 V AC
Overvoltage category input/output	III	Overvoltage category output/output	II
Pollution severity level	2	Pulse voltage test (1,2/50 μ s)	6 kV
Insulation test voltage	1.2 kVAC	Clearance input/output	\geq 5.5 mm

Creation date January 25, 2022 12:44:15 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

RSMS-8 24V+ BASE S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Connection field**

Clamping range, max.	6 mm ²	Clamping range, min.	0.13 mm ²
Flexible with sleeve, max.	2.5 mm ²	Flexible with sleeve, min.	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Max. wire cross-section, AWG	AWG 12	Min. wire cross-section, AWG	AWG 26
Sleeve with plastic collar, max.	2.5 mm ²	Solid, max. H05(07) V-U	6 mm ²
Solid, min. H05(07) V-U	0.5 mm ²	Stripping length	6 mm
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Type of connection	Screw connection		

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ECLASS 9.0	27-14-11-52
ECLASS 9.1	27-24-22-16	ECLASS 10.0	27-14-11-52
ECLASS 11.0	27-14-11-52		

Approvals

Approvals



ROHS	Conform
UL File Number Search	E141197

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Product Change Notification	20210818 Technical change to RSMS relay interfaces
Catalogues	Catalogues in PDF-format
Brochures	

RSMS-8 24V+ BASE S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1456810000](#)