

WSI 25/2 10X38 1KV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

In some applications it is useful to protect the feed through connection with a separate fuse. Fuse terminal blocks are made up of one terminal block bottom section with a fuse insertion carrier. The fuses vary from pivoting fuse levers and pluggable fuse holders to screwable closures and flat plug-in fuses.

General ordering data

Version	W-Series, Fuse terminal, Rated cross-section: 25 mm ² , Screw connection
Order No.	1469110000
Type	WSI 25/2 10X38 1KV
GTIN (EAN)	4050118277685
Qty.	6 pc(s).

Creation date September 16, 2022 6:00:45 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

WSI 25/2 10X38 1KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	58 mm	Depth (inches)	2.283 inch
Height	81 mm	Height (inches)	3.189 inch
Width	36 mm	Width (inches)	1.417 inch
Net weight	58.333 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	PA 66/6	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35	N-function	No
PE function	No	PEN function	No

2 clampable conductors (H05V/H07V) with equal cross-section (rated connection)

Wire connection cross section, finely stranded, two clampable wires, min.	0.75 mm ²	Wire cross-section, finely stranded, two clampable wires, max.	10 mm ²
---	----------------------	--	--------------------

Additional technical data

Type of mounting	Snap-on
------------------	---------

CSA rating data

Certificate No. (CSA)	238018-1868186	Wire cross section max. (CSA)	8 AWG
Wire cross section min. (CSA)	18 AWG		

WSI 25/2 10X38 1KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Conductors for clamping (rated connection)

Clampable conductor		Connection specification		Screw connection		
Clampable conductor	Cross-section for conductor connection	Type	solid, H05(07) V-U			
		min.	1.5 mm ²			
		max.	25 mm ²			
		nominal	25 mm ²			
	wire end ferrule	Stripping length	min.	11 mm		
			max.	11 mm		
			nominal	11 mm		
		Tightening torque	min.	2 Nm		
	max.		2.5 Nm			
	Recommended wire-end ferrule					
	Clampable conductor	Cross-section for conductor connection	Type	stranded, H07V-R		
			min.	1.5 mm ²		
max.			25 mm ²			
nominal			25 mm ²			
wire end ferrule		Stripping length	min.	11 mm		
			max.	11 mm		
			nominal	11 mm		
		Tightening torque	min.	2 Nm		
max.			2.5 Nm			
Recommended wire-end ferrule						
Clampable conductor		Cross-section for conductor connection	Type	flexible, H05(07) V-K		
			min.	1.5 mm ²		
	max.		25 mm ²			
	nominal		25 mm ²			
	wire end ferrule	Stripping length	min.	11 mm		
			max.	11 mm		
			nominal	11 mm		
		Tightening torque	min.	2 Nm		
	max.		2.5 Nm			
	Recommended wire-end ferrule					
	Connection direction	on side				
	Number of connections	4				
Stripping length	11 mm					
Type of connection	Screw connection					

General

Rail	TS 35	Standards	IEC 60269-1
------	-------	-----------	-------------

Rating data

Rated cross-section	25 mm ²	Rated voltage	1,000 V
Rated voltage to adjoining terminal	1,000 V	Rated DC voltage	1,000 V DC
Rated current	32 A	Current at maximum wires	32 A
Standards	IEC 60269-1	Volume resistance according to IEC 60947-7-x	0.32 mΩ
Rated impulse withstand voltage	6 kV	Power loss in accordance with IEC 60947-7-x	3.23 W
Pollution severity	3		

Creation date September 16, 2022 6:00:45 AM CEST

WSI 25/2 10X38 1KV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC000899	ETIM 7.0	EC000899
ETIM 8.0	EC000899	ECLASS 9.0	27-14-11-16
ECLASS 9.1	27-14-11-16	ECLASS 10.0	27-14-11-16
ECLASS 11.0	27-14-11-16	ECLASS 12.0	27-14-11-16

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	EAC certificate CE Declaration of Conformity UKCA Declaration of Conformity
Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format


Data sheet

WSI 25/2 10X38 1KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1469110000](#)