

**IE-SW-BL06T-4POE-2SC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

- 4 x IEEE 802.3af/at compliant PoE ports
- 12/24/48 VDC redundant wide-range power supply
- Integrated DC/DC converter for supplying 48 V PoE devices over the entire input voltage range from 12 to 57 VDC
- Intelligent power consumption detection and classification
- Variations with copper and fibre-optic interface (multimode and singlemode)

**General ordering data**

Version	Network switch, unmanaged PoE, Fast Ethernet, Number of ports: 4x RJ45 10/100 BaseT(X) PoE+, 2x SC Multi-mode, IP30, -40 °C...75 °C
Order No.	<a href="#">1504220000</a>
Type	IE-SW-BL06T-4POE-2SC
GTIN (EAN)	4050118312072
Qty.	1 pc(s).

Creation date January 26, 2022 5:30:15 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## IE-SW-BL06T-4POE-2SC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	115 mm	Height (inches)	4.528 inch
Width	50 mm	Width (inches)	1.969 inch
Net weight	375 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## EMC conformity and approvals

EMC standards	FCC Part 15 Subpart B Class A, EN 55032, EN 55024, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 GHz: 20 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 1 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, EN 61000-4-8	Free fall	According to IEC 60068-2-32
Safety standard	UL 508	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

## Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

## Fibre optic transceiver characteristics

Transmission rate	100 Mbps	
Transceiver type	Multimode	
Connector type	SC-Duplex	
Transmission distance, typ.	5 km	
Wavelength	typ.	1,300 nm
	Wavelength	TX
	min.	1,260 nm
	max.	1,360 nm
	Wavelength	RX
	min.	1,100 nm
Receive power	min.	-32 dBm
	max.	-3 dBm

Creation date January 26, 2022 5:30:15 AM CET

## IE-SW-BL06T-4POE-2SC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Transmission power	min.	-20 dBm
	max.	-10 dBm
Link-budget	12 dB	

### Guarantee

Time interval	5 years
---------------	---------

### Interfaces

Fibre-optic ports	100BaseFX ports (SC connector), Multimode	Function DIP switch	1x for enabling/disabling the broadcast storm protection
LED indicator	PWR1, PWR2, 10/100M (TP-Port), 100M (fibre-optic port), PoE	Number of ports	4x RJ45 10/100 BaseT(X) PoE+, 2x SC Multi-mode
RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port		

### MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	1,289,258 h

### Power over Ethernet (PoE)

PoE output current	Standard	IEEE 802.3af
	Output current	350 mA
	Standard	IEEE 802.3at
	Output current	600 mA
PoE output power	Standard	IEEE 802.3af
	Output power	15.4 W
	Standard	IEEE 802.3at
	Output power	30 W
PoE pin assignment	Mode A: Pin 1, 2 (V+); Pin 3, 6 (V-); Alternative A; MDI	
Total PoE power budget	Voltage type	DC
	Voltage, min.	12 V
	Voltage, max.	17 V
	Power budget	62 W
	Voltage type	DC
	Voltage, min.	18 V
	Voltage, max.	57 V
	Power budget	120 W

### Power supply

Connection type	1 removable 4-pin terminal block	
Current consumption	Voltage	12 V DC
	Current	6.19 A
	Voltage	24 V DC
	Current	5.55 A
	Voltage	48 V DC
	Current	2.71 A
Inrush current	64.56 A at 48 V DC (0.1 to 1 ms)	
Overload current protection	Yes	
Power consumption	max. 13.2 W (without PD's consumption)	

Creation date January 26, 2022 5:30:15 AM CET

## IE-SW-BL06T-4POE-2SC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Power loss	36.4 BTU/h		
Reverse polarity protection	Yes		
Voltage supply	12/24/48 V DC, 2 redundant inputs		
Voltage supply range	Voltage type	DC	
	Voltage, min.	12 V	
	Voltage, max.	57 V	

## Switch characteristics

MAC table size	2 K	Packet buffer size	768 Kbit
----------------	-----	--------------------	----------

## Technical data

Housing main material	Aluminium	Protection degree	IP30
Speed	Fast Ethernet	Switch	unmanaged PoE
Type of mounting	DIN rail, Panel (with optional mounting kit)		

## Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3af for Power-over-Ethernet, IEEE 802.3at for Power-over-Ethernet, IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3x for flow control		

## Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ECLASS 9.0	19-17-01-06
ECLASS 9.1	19-17-01-06	ECLASS 10.0	19-17-04-02
ECLASS 11.0	19-17-04-02		

## Approvals

Approvals



ROHS	Conform
UL File Number Search	E141197

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Product Change Notification	<a href="#">Product Change Notification IE-SW-BL06-PoE-series</a>
User Documentation	<a href="#">Hardware Installation Guide</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

Creation date January 26, 2022 5:30:15 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

4

## IE-SW-BL06T-4POE-2SC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

# Accessories

## Mounting kit for 19" rack assembly


- For assembling DIN rail-based devices on 19" racks



### General ordering data

Type	RM-KIT	Version
Order No.	<a href="#">1241440000</a>	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	

## Mounting kit for wall mounting



Mounting kit for alternative wall-mounting of DIN rail-based (top-hat type) Industrial Ethernet components.

**IE-WALLMOUNT-KIT-30MM** for use with:

- Industrial Ethernet Switches of the product range **IE-SW-BL05**

**IE-WALLMOUNT-KIT-46MM** for use with:

- Industrial Ethernet Switches of the product ranges **IE-SW- BL06/BL08/VL05/VL08/VL09/VL16/PL06/PL08/PL09/PL10/PL16/PL18**
- Industrial Ethernet media converters of the product range **IE-MC-VL**
- Industrial Ethernet switches of the product range **IE-WL-AP**

### General ordering data

Type	IE-WALLMOUNT-KIT-46MM
Order No.	<a href="#">1504440000</a>
GTIN (EAN)	4050118312317
Qty.	1 pc(s).

## IE-SW-BL06T-4POE-2SC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Ethernet (Cat.6)



- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

### General ordering data

Type	VDATA CAT6	Version
Order No.	<a href="#">1348590000</a>	Terminal rail fixing, Surge protection, Cat.6, 802.3 at Type 1, 802.3 at
GTIN (EAN)	4050118153002	Type 2, 802.3 bt Type 3, U <sub>p</sub> (L/N-PE) ≤ 550 V
Qty.	1 pc(s).	

### SC-Duplex



Mounting rail outlet, SC duplex junction design according to IEC 61754-4

### General ordering data

Type	IE-TO-SCD-MM	Version
Order No.	<a href="#">8946970000</a>	Mounting rail outlet, fibre-optic, SC duplex, Multimode, POF, IP20
GTIN (EAN)	4032248734979	
Qty.	10 pc(s).	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1504220000](#)