

THM WO 12/18 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 1.9 - 1.9 mm, 12 x 18 mm, yellow
Order No.	1856630000
Type	THM WO 12/18 GE
GTIN (EAN)	4032248399574
Qty.	1 pc(s).

Creation date January 28, 2022 11:43:54 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

THM WO 12/18 GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	12 mm	Height (inches)	0.472 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	489 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Polyacrylate adhesive	Colour	yellow
Halogen	No	Material	Polyester film
Material colour according to resistance code	4	Number of markers per combination	1 Label reel = Conductor and cable markers
Number per roll	10,000	Operating temperature range	-40...150 °C
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Size of labelling field	12 x 9 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	18 mm		

Conductor and cable markers

Conductor O.D.	1.9 - 1.9 mm	Conductor O.D., max.	1.9 mm
Conductor O.D., min.	1.9 mm	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 6 mm ²
Halogen	No	Text field height	9 mm
Text field width	12 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

Data sheet

THM WO 12/18 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM WO 12/18 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1856630000](#)