

**SAIE-M12B-4-0.5U-FP-M16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

**General ordering data**

Version	Built-in plugs, M12, Female socket, straight, M 16, Number of poles: 4, 0.5 m, Front mounting
Order No.	<a href="#">1861190000</a>
Type	SAIE-M12B-4-0.5U-FP-M16
GTIN (EAN)	4032248419265
Qty.	1 pc(s).

Creation date January 28, 2022 12:10:20 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## SAIE-M12B-4-0.5U-FP-M16

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight 31 g

## Environmental Product Compliance

REACH SVHC Lead 7439-92-1

## Technical data customisable plug-in connectors

Cable glands	M 16	Coding	A
Contact surface	Gold-plated	Housing main material	Zinc diecast
Number of poles	4	Plugging cycles	≥ 100
Protection degree	IP67, when screwed in	Rated current	4 A
Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)	Rated voltage	250 V
Rated voltage	250 V (4-pole)/ 60 V (5-pole)/ 30 V (8 and 12-pole)	Temperature range of housing	-30...+90 °C

## Standards

Connector standard IEC 61076-2-101

## General data

Cable glands	M 16	Cable length	0.5 m
Coding	A	Conductor O.D.	-
Connection thread	M12	Contact surface	Gold-plated
Core cross-section	0.34 mm <sup>2</sup>	Housing main material	Zinc diecast
Material	PVC	Mounting thread	M 16
Number of poles	4	Plugging cycles	≥ 100
Protection degree	IP67, when screwed in	Rated current	4 A
Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)	Rated voltage	250 V
Rated voltage	250 V (4-pole)/ 60 V (5-pole)/ 30 V (8 and 12-pole)	Strand / cable length	0.5 m
Temperature range of housing	-30...+90 °C	Type of mounting	Front mounting
Wire cross section (Print/Online)	0.34 (4- and 5-pole)/ 0.25 (8-pole)/ 0.14 (12-pole)		

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC003570
ETIM 8.0	EC003570	ECLASS 9.0	27-44-01-03
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-03
ECLASS 11.0	27-44-01-03		

## Approvals

Approvals



ROHS Conform

Creation date January 28, 2022 12:10:20 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

2

**SAIE-M12B-4-0.5U-FP-M16**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

---

**Data sheet**


**SAIE-M12B-4-0.5U-FP-M16**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Wiring diagram**



**Pole scheme**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1861190000](#)