

IE-C5CS8VG-100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Bulk stock, copper cable, rigid, 4 x 2 x AWG 24/1, Cat. 5,
green

General ordering data

Version	Installation cable, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 100 m
Order No.	8813150000
Type	IE-C5CS8VG-100
GTIN (EAN)	4032248512904
Qty.	1 pc(s).

Creation date January 30, 2022 9:26:59 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

IE-C5CS8VG-100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	100 m	Length (inches)	3,937.008 inch
Net weight	4,720 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-15 °C...60 °C		

Technical specifications for cable

Insulation	PE	Number of poles	8
Number of wires	8	Resistance to spread of flame	in accordance with IEC 60332-1
Sheathing colour	green (RAL 6018)	Test voltage: wire-wire-shield	700 V AC

Cable structure

Arrangement of wire cores	Twisted pair	Colour sequence or wires - wire pairs	white/blue - blue, white/ orange - orange, white/ green - green, white/ brown - brown
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*2*AWG 24/1 - 4*2*0.205 mm ²
Diameter of wire pair	2 mm	Insulation	PE
Insulation cross-section	1 mm	Material sheath	PVC
Number of wires	8	Overlap of shielding braid	65 %
Sheath diameter, max.	6.3 mm	Sheath diameter, min.	5.7 mm
Sheathing colour	green (RAL 6018)	Sheathing material thickness	0.55 mm
Shielding	SF/UTP	Shielding braid thickness	0.1 mm
Standard designations	IE-5CC4x2xAWG26/7- PVC LI02YS(ST)CY, SF/ UTP	Strands	1
Wire core insulation thickness	0.25 mm	Wire material	Non-insulated copper wire

Electrical properties of cable

Capacity at 1 kHz	47 nF/km	Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Characteristic impedance	100 ± 5 Ω at 100MHz	Deviation	40 ns/100m
Loop resistance	290 Ω/km	Resistance differential	3 %
Signal propagation time	4.85 ns/m	Test voltage: wire-wire-shield	700 V AC
Transfer impedance	10 mΩ/m at 10 MHz		

Mechanical and material properties of cable

Abrasion resistance	good	Colour	green
Fire propagation	No	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	10 x cable diameter	Resistance to spread of flame	in accordance with IEC 60332-1

IE-C5CS8VG-100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Classifications**

ETIM 6.0	EC000830	ETIM 7.0	EC003249
ETIM 8.0	EC003249	ECLASS 9.0	27-06-18-05
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-18-01
ECLASS 11.0	27-06-18-01		

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

Data sheet


IE-C5CS8VG-100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing



IE-C5CS8VG-100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Tools**

The CST with blue blade cartridge produces the best stripping results. The blue double-stage blade cartridge is particularly suited for Ethernet cables. It saves time and also ensures optimal stripping results.

General ordering data

Type	IE-CST	Version
Order No.	9204350000	Tools, Sheathing strippers
GTIN (EAN)	4032248653072	
Qty.	1 pc(s).	

Tools

Sheathing stripper for PVC cables

**General ordering data**

Type	AM 12	Version
Order No.	9030060000	Tools, Sheathing strippers
GTIN (EAN)	4008190337827	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8813150000](#)