


SMPM FEMALE
INTERFACE
PER MIL-STD-348
BOTH ENDS

FREQUENCY GHz	RETURN LOSS	VSWR
DC to 15.0	35 dB	1.03:1
15.0 TO 25.0	23 dB	1.15:1
25.0 to 40.0	20 dB	1.22:1

COMPONENT		MATERIAL & FINISH		 MICRO-MODE PRODUCTS, INC. <i>The Reliable Connection to the Future</i>	El Cajon, CA 92020 ph 619.449.3844 www.micromode.com	CAGE CODE 15907
BODY & CONTACT		BeCu, ASTM B196, UNS C17300 GOLD PLATE, MIL-G-45204, TYPE 1, GRADE C, CLASS 1				
INSULATOR		PTFE, ASTM D1710, TYPE 1, GRADE 1, CLASS A		ASSY PROCEDURES: N/A INSERTION/EXTRACTION TOOL: MMTL-6460		SMPM FEMALE BLINDMATE INTERCONNECT, .211 OAL PART NO. MSSP-12580
				SHEET 1 OF 1 OL12580 5-23-13 MP .		

PART NO. MSSP-12580 | OUTLINE DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro-Mode:](#)

[MSSP-12580](#)