



General ordering data

Order No.	1930880000
Part designation	SV 7.62HP/08/180SF SW
Version	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 8, 180°, Box
EAN	4032248580859
Qty.	50 pc(s).

System parameters

Fitted to PCB	Soldered connection
Outgoing elbow	180°
Pitch	7.62 mm
Pitch in inch	0.3 inch
No. of poles	8
Solder pin length	3.5 mm
Dia. of fitting hole	1.3 mm
Fitting hole tolerance	+ 0.1 mm
L1 in mm	53.34 mm
L1 in inch	2.1 inch
Insulation resistance	1,000 MΩ

Material data

Insulating material	PA GF
Colour	black
colour chart	Similar to RAL 9011
Insulating material group	I
Flammability class UL 94	V-0
CTI	≥ 500
Contact base material	Copper alloy
Contact surface	tinned
Constant operating temp., min.	-25 °C
Constant operating temp., max.	125 °C
Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C

Material data

DIN IEC rating data

Rated current, min. No. pins (Tu=20°C)	41 A
Rated current, max. No. pins (Tu=20°C)	41 A
Rated current, min. No. pins (Tu=40°C)	41 A
Rated current, max. No. pins (Tu=40°C)	38 A
Rated voltage for overvoltage class/pollution severity III/3	630 V
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	6 kV
Rated voltage for overvoltage class/pollution severity III/2	630 V
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	6 kV
Rated voltage for overvoltage class/pollution severity II/2	1,000 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	6 kV

CSA rating data

Rated voltage (Use group C)	300 V
Rated current (Use group C)	35 A
Rated voltage (Use group D)	600 V
Rated current (Use group D)	5 A

UL 1059 rating data

Rated voltage (Use group C)	300 V
Rated current (Use group C)	35 A
Rated voltage (Use group D)	600 V
Rated current (Use group D)	5 A

Downloads

CAD Library (P-CAD Format - Standard)	SV.LIB
---------------------------------------	--------

Classifications

eClass 5.1	27-26-07-04
------------	-------------

Similar products

Order No.	Part designation	Version
1930820000	SV 7.62HP/02/180SF SW	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 2, 180°, Box
1930830000	SV 7.62HP/03/180SF SW	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 3, 180°, Box
1930840000	SV 7.62HP/04/180SF SW	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 4, 180°, Box
1930850000	SV 7.62HP/05/180SF SW	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 5, 180°, Box

1930860000	SV 7.62HP/06/180SF SW	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 6, 180°, Box
1930870000	SV 7.62HP/07/180SF SW	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 7, 180°, Box
1930890000	SV 7.62HP/09/180SF SW	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 9, 180°, Box
1930900000	SV 7.62HP/10/180SF SW	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 10, 180°, Box
1930910000	SV 7.62HP/11/180SF SW	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 11, 180°, Box
1930920000	SV 7.62HP/12/180SF SW	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 7.62 mm, No. of poles: 12, 180°, Box

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1930880000](#)