




PRODUCT BRIEF

Intel® Desktop Board D2500HN
Innovation Series



Mini-ITX Form Factor

Intel® Desktop Board D2500HN Innovation Series



The Intel® Desktop Board D2500HN is the latest Innovation Series board that optimizes the performance of the Intel® Atom™ processor D2500 and the Intel® NM10 Express Chipset by delivering new-generation technologies, value-added features, and easy integration. The Intel Desktop Board D2500HN is suitable for basic computing and powerful enough to enable a rich Internet experience.

The Intel Desktop Board D2500HN features the new integrated dual-core 1.86 GHz Intel Atom processor D2500. This processor supports Intel® Graphics Media Accelerator 3600, an improved graphics core that supports high-definition video playback capabilities compared with the previous-generation entry-level desktop PC. This

board provides flexibility and upgradability with two single-channel SODIMM connectors for DDR3 1066 / 800 MHz memory support (4 GB¹ max). The use of SODIMM memory modules delivers greater performance and power efficiency. The revolutionary two-chip layout continues to enable lower power consumption and saves 70 percent of its board layout size. This results in a board that has better heat flow with the passive thermal solution.

The Intel Desktop Board D2500HN provides enhanced features such as 10/100/1000 Mb/s integrated LAN, integrated four-channel Intel® High Definition Audio², and support for legacy features for emerging market needs, including a PS/2 port, serial port, and parallel port. Supporting a USB Solid-State Drive keep-out zone design, the

Intel Desktop Board D2500HN is ideal for diskless usage model by integrating the USB Solid-State Drive inside the chassis.

The Intel Desktop Board D2500HN is a mini-ITX form factor board. Backward-compatible with ATX and microATX, this form factor allows you to build green, energy-efficient, small form factor solutions. This board offers simple, affordable, Internet-centric computer designs in a compact 170mm x 170mm size—perfect for a cool system with a small form factor chassis.

Available at an affordable price, the Intel Desktop Board D2500HN is ideal for innovative small form factor systems for basic computing and thin-client systems.



Intel® Desktop Board D2500HN Innovation Series

The boxed Intel® Desktop Board D2500HN solution includes:

- ATX 2.2 compliant I/O shield
- SATA cables
- Board and back panel I/O layout stickers
- Quick reference guide
- Intel® Express Installer driver and software DVD
- Microsoft* Windows* 7 WHQL certified


The takeaway software included with the Intel® Desktop Board D2500HN works best for your everyday computing.

CAPABILITY	SOFTWARE INCLUDED:
Productivity	<ul style="list-style-type: none">▪ Intel AppUpSM▪ Intel® Integrator Assistant (Internet Download)▪ Laplink* PCmover Express*
Entertainment	<ul style="list-style-type: none">▪ DivX* for Windows*
Antivirus	<ul style="list-style-type: none">▪ ESET* Smart Security 4 (45-day license)

Intel® Desktop Board D2500HN Innovation Series

Features and Benefits

- 1 Integrated with the new dual-core Intel® Atom™ processor D2500:** Features an integrated graphics core (Intel® GMA 3600) with high-definition graphics performance improvements.
- 2 Intel® NM10 Express Chipset:** Designed to support the new Intel® Atom™ processor D2500.
- 3 Single-channel DDR3 with two connectors for 1066 / 800 MHz memory support (4 GB¹ max)**
- 4 One PCI connector:** Expansion connector for custom system configurations and future add-in card upgrades.
- 5 Two SATA ports (3.0 Gb/s)**
- 6 Four-channel Intel® High Definition Audio²:** Integrated stereo audio at an excellent value.
- 7 Integrated 10/100/1000 Mb/s Network Connection**
- 8 Eight Hi-Speed USB 2.0 ports:** Four back panel ports and four additional ports via internal header.
- 9 PS/2 port:** Supports keyboard or mouse.
- 10 Parallel and serial ports:** Provide legacy device compatibility.
- 11 Mini-ITX / microATX-compatible form factor**



Intel® Desktop Board D2500HN Innovation Series

Technical Specifications

For ordering information, visit www.intel.com

For the most current product information, visit <http://developer.intel.com/products/desktop/motherboard/>

PROCESSOR

Processor Support

- Intel® Atom™ processor D2500 (dual-core / 1.86 GHz / 512 KB x 2 L2 cache)

CHIPSET

- Intel® NM10 Express Chipset

Graphics

- Intel® Graphics Media Accelerator 3600
- One VGA port

I/O Controller

- Two SATA ports (fully shrouded)
- One PS/2 port
- One serial header
- One serial port
- One parallel port

USB 2.0

- Four external ports
- Four ports via headers

Audio Solution

- 2+2 channel Intel® High Definition Audio² (with multi-streaming)
- Front-panel mic / headphone header

10/100/1000 Network Connection

- Intel® 82574L 10/100/1000 Mb/s Ethernet Controller

System BIOS

- 8 Mb Flash EEPROM with Intel® Platform Innovation Framework for EFI Plug and Play, IDE drive auto-configure
- Advanced configuration and power interface V2.0b, DMI 2.0, multilingual support
- Serial Peripheral Interface (SPI) Flash

Fast Boot BIOS

- Optimized POST for almost instant-on access to PC from power-on

SYSTEM MEMORY

Memory Capacity

- Single-channel DDR3 with two connectors for 1066 / 800 MHz memory support (4 GB¹ max)

Memory Types

- DDR3 1066 / 800 SDRAM memory support
- Non-ECC Memory

Memory Voltage

- 1.8 V

Wake-up from Network

- Wired for Management (WfM) 2.0 compatible
- Support for system wake-up using an add-in network interface card with remote wake-up capability

Expansion Capabilities

- One PCI connector

JUMPERS AND FRONT PANEL CONNECTORS

Jumpers

- Jumper: yellow
- Header: black

Front-Panel Connectors

- Reset, HD LED, Power LEDs, power on/off, aux LED
- USB 2.0 headers
- Audio header

MECHANICAL

Board Style

- Mini-ITX / microATX-compatible
- 170mm x 170mm

Baseboard Power Requirements

- ATX12V or SFX12V

ENVIRONMENT

Operating Temperature

- 0°C to +50°C

Storage Temperature

- 20°C to +70°C

REGULATIONS AND SAFETY STANDARDS

United States and Canada

- UL 60950-1

Canada

- CAN / CSA-C22.2 No. 60950-1

Europe

- (Low Voltage Directive 2006/95/EC)
- EN 60950-1

International

- IEC 60950-1

EMC Regulations (Class B)

United States

- FCC CFR Title 47, Chapter I, Part 15, Subparts A / B

Canada

- ICES-003

Europe

- (EMC Directive 2004/108/EC)
- EN 55022 and EN 55024

Australia/New Zealand

- EN 55022

Japan

- VCCI V-3, V-4

South Korea

- KN-22 and KN-24

Taiwan

- CNS 13438

International

- CISPR 22

Environmental Compliance

Europe

- Europe RoHS (Directive 2002/95/EC)

China

- China RoHS (MII Order # 39)

¹ System resources and hardware (such as PCI and PCI Express*) require physical memory address locations that can reduce available addressable system memory. This could result in a reduction of as much as 1 GB or more of physical addressable memory being available to the operating system and applications, depending on the system configuration and operating system.

² Intel® High Definition Audio requires a system with an appropriate Intel® chipset and a motherboard with an appropriate codec and the necessary drivers installed. System sound quality will vary depending on actual implementation, controller, codec, drivers, and speakers. For more information about Intel® HD Audio, refer to www.intel.com/design/chipsets/hdaudio.htm

INFORMATION IN THIS DOCUMENT IS PROVIDED IN CONNECTION WITH INTEL® PRODUCTS. NO LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE, TO ANY INTELLECTUAL PROPERTY RIGHTS IS GRANTED BY THIS DOCUMENT. EXCEPT AS PROVIDED IN INTEL'S TERMS AND CONDITIONS OF SALE FOR SUCH PRODUCTS, INTEL ASSUMES NO LIABILITY WHATSOEVER, AND INTEL DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY, RELATING TO SALE AND/OR USE OF INTEL PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT, OR OTHER INTELLECTUAL PROPERTY RIGHT.


Intel products are not intended for use in medical, life-saving, or life-sustaining applications. Intel may make changes to specifications and product descriptions at any time, without notice.

All products, dates, and figures specified are preliminary based on current expectations, and are subject to change without notice. Availability in different channels may vary.

Actual Intel® Desktop Board may differ from the image shown.

Intel, the Intel logo, Intel Atom, Intel Atom Inside, and Intel AppUp are trademarks of Intel Corporation in the U.S. and other countries.

* Other names and brands may be claimed as the property of others.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Intel:](#)

[BOXD2550MUD2](#) [BOXD2500HN](#)