



### Bestückungsplan / contact layout

■ bestückt / assembled



### Leiterplatten-Lochbild Vorschlag / PCB drillhole pattern proposal



Elastische Einpresszone / compliant pressfit zone  
 Isolierwerkstoff / housing material: PBT GF30  
 Bauart 7 / type 7  
 Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles  
 Fehlende Masse und Angaben nach IEC 60 603-2 / DIN EN 60 603-2  
 Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2  
 Schichtaufbau im metallisierten Loch siehe Zeichnung 164062 / Nr. 10  
 diameter of drilled hole see drawing 164062 / No. 10  
 1)  $\phi 1.6^{+0.09}_{-0.06}$  Durchmesser des metallisierten Loches  
 $\phi 1.6^{+0.09}_{-0.06}$  Diameter of finished plated-through hole

Information:		Tolerances	All Dimensions in mm	Scale 2:1
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation <b>Federleiste D 32 EE</b> <b>Fem. Connector D 32 Pressfit</b>
www.ERNI.com		354445		I A3
c	23.04.2013	Class		STVD
Index	Date			

Copyright by ERNI GmbH  
 Proprietary notice pursuant to ISO 9006 to be observed.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[354445](#)