



SUCCESSIVE DETECTION LOG VIDEO AMPLIFIER (SDLVA) WITH LIMITED RF OUTPUT, 1 - 26 GHz

Typical Applications


The HMC813 is ideal for:

- EW, ELINT & IFM Receivers
- DF Radar Systems
- ECM Systems
- Broadband Test & Measurement
- Power Measurement & Control Circuits
- Military & Space Applications

Features

- 1 to 26 GHz Operation
- High Logging Range: 55 dB
- Frequency Flatness: ± 1.5 dB
- Saturated Output Power: -7 dBm
- Fast Rise/Fall Times: 4/10 ns
- Single Positive Supply: +3.3V
- ESD Sensitivity (HBM): Class 1A
- 55 to +85° C Operating Temperature

Functional Diagram



General Description

The HMC813 is a Successive Detection Log Video Amplifier (SDLVA) With Limited RF which operates from 1 to 26 GHz. The HMC813 provides a logging range of 55 dB. This device offers typical fast rise/fall times of 4/10 ns. The HMC813 log video output slope is typically 14.5 mV/dB. Maximum recovery times are less than 20 ns. Ideal for high speed channelized receiver applications, the HMC813 operates from a single +3.3 V supply, and consumes only 150 mA. All data shown herein is measured with the chip in a 50 Ohm environment and contacted with RF probes.

Electrical Specifications, $T_A = +25^\circ\text{C}$, $V_{CC1} = V_{CC2} = V_{CC3} = V_{CC4} = 3.3\text{V}$ [1]

| Parameter | Conditions | Typ. | Units |
|--------------------------------------|------------------------------|-----------|-------|
| Input Frequency Range ^[2] | | 1 - 26 | GHz |
| Frequency Flatness (Video out) | Pin = -25 dBm | ± 1.5 | dB |
| Log Linearity | Pin = -40 dBm to +0 dBm | ± 1 | dB |
| Log Linearity over Temperature | -55 to +85° C, Pin = -20 dBm | ± 0.5 | dB |
| Minimum Logging Range | to ± 3 dB error @ 18 GHz | -53 | dBm |
| Maximum Logging Range | to ± 3 dB error @ 18 GHz | 6 | dBm |
| Saturated Output Power, Psat | | -7 | dBm |
| Saturated Output Power Flatness | | ± 2.5 | dB |
| RF Input Return Loss | | 7 | dB |
| RF Output Return Loss | | 13 | dB |
| Log Video Minimum Output Voltage | | 0.875 | V |
| Log Video Maximum Output Voltage | | 1.65 | V |
| Log Video Output Rise Time | Pin = 0 dBm, 10% to 90% | 4 | ns |
| Log Video Output Fall Time | Pin = 0 dBm, 90% to 10% | 10 | ns |

[1] Electrical specs and performance plots are given for single-ended operation.

[2] Video output load should be 1K Ohm or higher.

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

For price, delivery, and to place orders: Analog Devices, Inc., One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106 Phone: 781-329-4700 • Order online at www.analog.com Application Support: Phone: 1-800-ANALOG-D




SUCCESSIVE DETECTION LOG VIDEO AMPLIFIER (SDLVA) WITH LIMITED RF OUTPUT, 1 - 26 GHz

Electrical Specifications, (continued) ^[1]


| Parameter | Conditions | Typ. | Units |
|---------------------------------------------------|------------------|------|--------------------------------|
| Log Video Recovery Time | -50 dBm to 0 dBm | 20 | ns |
| Log Video Output Slope | | 14.5 | mV/dB |
| Log Video Output Slope Variation over Temperature | @ 10 GHz | 3 | $\mu\text{V/dB}^\circ\text{C}$ |
| Log Video Propagation Delay | | 15 | ns |
| Supply Current (I _{dc}) | | 150 | mA |

[1] Electrical specs and performance plots are given for single-ended operation


**VIDEO OUT & Error
vs. Input Power, $f_{in} = 1$ GHz ^[1]**




**VIDEO OUT & Error
vs. Input Power, $f_{in} = 2$ GHz ^[1]**



**VIDEO OUT & Error
vs. Input Power, $f_{in} = 6$ GHz ^[1]**



**VIDEO OUT & Error
vs. Input Power, $f_{in} = 10$ GHz ^[1]**




[1] Electrical specs and performance plots are given for single-ended operation




**SUCCESSIVE DETECTION LOG VIDEO AMPLIFIER (SDLVA)
WITH LIMITED RF OUTPUT, 1 - 26 GHz**


**VIDEO OUT & Error
vs. Input Power, $F_{in} = 14$ GHz ^[1]**




**VIDEO OUT & Error
vs. Input Power, $F_{in} = 18$ GHz ^[1]**




**VIDEO OUT vs. Error
vs. Input Power, $F_{in} = 20$ GHz ^[1]**



**VIDEO OUT & Error
vs. Input Power, $F_{in} = 22$ GHz ^[1]**



**VIDEO OUT & Error
vs. Input Power, $F_{in} = 26$ GHz ^[1]**




[1] Electrical specs and performance plots are given for single-ended operation




SUCCESSIVE DETECTION LOG VIDEO AMPLIFIER (SDLVA) WITH LIMITED RF OUTPUT, 1 - 26 GHz


**VIDEO OUT vs. Frequency
Over Input Power & Temperature ^[1]**




**Saturated RF Output Power vs. Frequency
Over Temperature @ Pin = -10 dBm ^[1]**




**RF Output Power vs. Input Power
Over Frequency ^[1]**




**Return Loss vs. Frequency
Over Temperature ^[1]**



**Rise Time @ Fin = 10 GHz @ Pin = 0 dBm
Over Temperature ^[1]**



**Fall Time @ Fin = 10 GHz @ Pin = 0 dBm
Over Temperature ^[1]**



[1] Electrical specs and performance plots are given for single-ended operation



SUCCESSIVE DETECTION LOG VIDEO AMPLIFIER (SDLVA) WITH LIMITED RF OUTPUT, 1 - 26 GHz

Absolute Maximum Ratings

| | |
|------------------------------------------------------------|----------------|
| Vcc1, Vcc2, Vcc3, Vcc4 | +3.6V |
| ENBL | +3.6V |
| RF Input Power | +15 dBm |
| Channel Temperature | 125 °C |
| Continuous Pdiss (T=85°C) Derate 12.63 mW/°C above 85°C | 0.51 W |
| Thermal Resistance (Channel to die bottom) | 79.20 °C/W |
| Storage Temperature | -65 to +150 °C |
| Operating Temperature | -55 to +85 °C |
| ESD Sensitivity (HBM) | Class 1A |

Die Packaging Information ^[1]

| Standard | Alternate |
|--------------------|-----------|
| WP-3 (Waffle Pack) | [2] |

[1] Refer to the "Packaging Information" section for die packaging dimensions.

[2] For alternate packaging information contact Hittite Microwave Corporation.


NOTES:

1. ALL DIMENSIONS IN INCHES [MILLIMETERS]
2. DIE THICKNESS IS 0.011 [0.28]
3. TYPICAL BOND PAD IS 0.0024 SQUARE
4. BOND PAD METALLIZATION: ALUMINUM
5. NO BACKSIDE METAL
6. NO CONNECTION REQUIRED FOR UNLABELED BOND PADS
7. OVERALL DIE SIZE IS ±.002

Outline Drawing



**ELECTROSTATIC SENSITIVE DEVICE
OBSERVE HANDLING PRECAUTIONS**








Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

For price, delivery, and to place orders: Analog Devices, Inc.,
One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106
Phone: 781-329-4700 • Order online at www.analog.com
Application Support: Phone: 1-800-ANALOG-D



SUCCESSIVE DETECTION LOG VIDEO AMPLIFIER (SDLVA) WITH LIMITED RF OUTPUT, 1 - 26 GHz



Pad Descriptions

| Pad Number | Function | Description | Interface Schematic |
|--------------------------------------------|-------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 1 -4, 31 | VCC1 | Bias supply. Connect supply voltage to these pads with appropriate filtering. See application circuit. To ensure proper start-up supply rise time should be faster than 100usec |  |
| 6, 7 | VCC3 | | |
| 8, 9 | VCC4 | | |
| 5 | VCC2 | Bias supply. Connect supply voltage to this pad with appropriate filtering. See application circuit. To ensure proper start-up supply rise time should be faster than 100usec |  |
| 10 | EN | Enable pad, connected to supply voltage for normal operation. Total supply current reduced to less than 3mA when EN is set to 0V. |  |
| 11, 14 - 17, 20 - 26, 29, 30 Die Bottom | GND | Die bottom must be connected to RF and DC ground. |  |
| 12, 13 | RFOUT+, RFOUT- | RF Output pads. AC couple RF to RF OUT+, and AC couple RF OUT- to ground via 50 Ohm for single ended operation. |  |



SUCCESSIVE DETECTION LOG VIDEO AMPLIFIER (SDLVA) WITH LIMITED RF OUTPUT, 1 - 26 GHz


Pad Descriptions (Continued)

| Pad Number | Function | Description | Interface Schematic |
|------------|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
| 18, 19 | VIDEO FB, VIDEO OUT | Video out and feedback. These pins should be shorted to each other (see application circuit). Video out load should be at least 1K Ohm or higher. |  |
| 27, 28 | RFIN-, RFIN+ | RF Input pads. Connect RF to RF IN+, and AC couple RF IN- to ground via 50 Ohm for single ended operation. |  |



**SUCCESSIVE DETECTION LOG VIDEO AMPLIFIER (SDLVA)
WITH LIMITED RF OUTPUT, 1 - 26 GHz**

Application Circuit




Note: Video output load should be 1K Ohm or higher.



SUCCESSIVE DETECTION LOG VIDEO AMPLIFIER (SDLVA) WITH LIMITED RF OUTPUT, 1 - 26 GHz

Assembly Diagram



List of Materials for Assembly Diagram

| Item | Description |
|------------------|------------------------------------------------------|
| C3 - C6 | 100 pF SLC Capacitor, Presidio SA1212BX101M16VHXF |
| C7 - C10 | 10 nF SLC Capacitor, Presidio MVB3030X103ZGH5N |
| C1, C2, C11, C12 | 33 pF Capacitor, 0402 Pkg. |
| R1, R2 | 50 Ohm Resistor, 0402 Pkg. |
| R3 | 10 Ohm Resistor, 0402 Pkg. |
| R4 | 1k Ohm Resistor, 0402 Pkg. |
| U1 | HMC813 Die |



**ELECTROSTATIC SENSITIVE DEVICE
OBSERVE HANDLING PRECAUTIONS**



SUCCESSIVE DETECTION LOG VIDEO AMPLIFIER (SDLVA) WITH LIMITED RF OUTPUT, 1 - 26 GHz

Mounting & Bonding Techniques for MMICs

The die should be attached directly to the ground plane with epoxy (see HMC general Handling, Mounting, Bonding Note).

50 Ohm Microstrip transmission lines on 0.254mm (10 mil) thick alumina thin film substrates are recommended for bringing RF to and from the chip (Figure 1).

Microstrip substrates should be placed as close to the die as possible in order to minimize bond wire length. Typical die-to-substrate spacing is 0.076mm to 0.152 mm (3 to 6 mils).

Handling Precautions

Follow these precautions to avoid permanent damage.

Storage: All bare die are placed in either Waffle or Gel based ESD protective containers, and then sealed in an ESD protective bag for shipment. Once the sealed ESD protective bag has been opened, all die should be stored in a dry nitrogen environment.

Cleanliness: Handle the chips in a clean environment. DO NOT attempt to clean the chip using liquid cleaning systems.


Static Sensitivity: Follow ESD precautions to protect against ESD strikes. HMC813 is a Class-1A ESD sensitive part. Observe handling precautions.

Transients: Suppress instrument and bias supply transients while bias is applied. Use shielded signal and bias cables to minimize inductive pick-up.

General Handling: The chip may be handled by a vacuum collet or with a sharp pair of tweezers.

Mounting

Epoxy Die Attach: Apply a minimum amount of epoxy to the mounting surface so that a thin epoxy fillet is observed around the perimeter of the chip once it is placed into position. Cure epoxy per the manufacturer's schedule.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Analog Devices Inc.:](#)

[HMC813](#) [HMC813-SX](#)