

# Holder

46-  
2V00.000.000



<https://eao.com/p/46-2V00.000.000>

Your product:

---



## 46-2V00.000.000 Holder

### FRONT

**Colour:** Grey

### MOUNTING

**Mounting type:** Panel mounting

### ELECTRICAL CHARACTERISTICS

**Protection class:** II

### MECHANICAL CHARACTERISTIC

**Tightening torque:** 0.8 ... 1 Nm for screw terminal

**Weight:** 0.016 kg

### AMBIENT CONDITION

**IP front protection:** IP20

**Operating temperature:** – 25 °C ... + 55 °C

**Shock resistance:** 30g, 18ms (EN-IEC 60068-2-27)  
50g, 11ms (EN-IEC 60068-2-27)

**Vibration resistance:** 5g f= 2...500Hz (EN-IEC 60068-2-6)

**Climate resistance:** +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

### CERTIFICATE

**Approbations:** CSA, EAC, UL

**Conformities:** CE

|                   |                                                    |
|-------------------|----------------------------------------------------|
| <b>REACH:</b>     | REACH compliant                                    |
| <b>RoHS:</b>      | RoHS compliant                                     |
| <b>Standards:</b> | CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508 |

## OTHER


**Short Description:** Holder, Plastic

**Dimension:** 38 mm x 30 mm


**Material:** Plastic

**Colour RAL:** 7016 RAL

**Wiring diagrams:**



**Dimension drawings:**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[46-2V00.000.000](#)