


# EAO – Your Expert Partner for Human Machine Interfaces

## 84-8005.7640 - Illumination element with bi-colour illumination

### 84-8005.7640 - Illumination element with bi-colour illumination



*Attention: The preview is based on a sample product. This can differ from your current configuration.*

#### Other Attributes

Weight	0,011 kg
Operating voltage	24 V DC $\pm$ 10 %
Operation current	15 mA

#### IP-Rating

Protection degree	IP67
-------------------	------

#### Connection Method

Terminal	Flat ribbon cable
----------	-------------------


#### Illumination

LED colour	
------------	--

# EAO – Your Expert Partner for Human Machine Interfaces

84-8005.7640 - Illumination element with bi-colour illumination

## Wiring diagram



## Additional information

LED and built-in resistor included

Standard version: Cable length 300 mm with insulated ferrule, plug-in terminal 2.8 x 0.8 mm

Other options on request: Customisation of cable and connectors, rear side fully sealed (IP 67).

Best illumination level will be reached with aluminium lens with spot, Part No. 84-7215.x00 and 84-7211.x00

Protection degree (rear side): IP 40, upgrade to IP 67 with plug Part No. 84-900 possible. With applications where strong vibrations occur, the plugs may become loose

Cable connection IP 67, rear side fully sealed. The illumination element of the cable version cannot be disconnected from the actuator any longer

Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EAO:

[84-8005.7640](tel:84-8005.7640)