


VSRAM — Right Angle Male

VSRAM signal-integrity connectors are used in right angle, PCB-mount applications where a male interface is required. Termination styles include press-fit, paste-in-hole or plated thru-hole. Pitch: 1.27 mm.



Sample Part Number Format: VSRAM-04-10-50-50-02-G

VSRAM	—	□	—	□	—	50	—	□	—	□
SERIES Right Angle (Male) 1.27 mm		ROWS 04 – 4 Rows 05 – 5 Rows 06 – 6 Rows 08 – 8 Rows 10 – 10 Rows		COLUMNS 10 – 10 Columns 20 – 20 Columns 30 – 30 Columns 40 – 40 Columns 50 – 50 Columns		CONTACT PLATING 50 – 50 μ" Au		TERMINATION 00 – Press-fit 01 – Paste-in-hole 02 – PTH 0.078" 03 – PTH 0.109" 04 – PTH 0.140" 05 – PTH 0.156" 06 – PTH 0.172"		OPTIONS Blank – No options* G – Guide pin N – Fixed jacknut J – Turning jackscrew L – Locking screw

Notes:

See AirBorn spec ESL5001 for installation information.
Connector potting is standard.

* No hardware supplied with blank hardware option connectors.

AirBorn can manufacture other configurations to your exact specifications.

RoHS Compliant; certificate of conformance available upon request with each shipment.


Please view document VSRAM-XX-XX-XX-XX-X on airborn.com before part configuration for more product specification information.

NOTE: Please consult airborn.com to configure your part number and for the latest revision controlled drawing and technical data.

Reliable Contact Every Time

VerSI connectors feature a low-mating-force, high-reliability contact system with four points-of-contact.

The open-pin field design allows flexibility in termination schemes. Single-ended, differential pair, power, and ground are all available in one connector design.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AirBorn:](#)

[VSRAM-05-30-50-00-J](#)