

ECU-1260

Cortex-A35 Industrial Communication Gateway

NEW



CE FCC RoHS

Features

- Cortex-A35 Quad Core, 1GHz CPU
- Supports web service for remote on-line monitoring
- Supports SD card & on-line firmware update
- Supports Modbus, IEC-60870-101/104 protocol
- Supports data logger on SD card
- Operating temperature -40~70°C

Introduction

Advantech has introduced the ECU-1260, an industrial communication gateway designed for applications related to solar power, electricity, and factory operations that demand comprehensive wireless and Ethernet communication solutions. The ECU-1260 is equipped with a Cortex A35 processor, up to three RS-232/485 isolated serial ports, two Ethernet ports, and can operate within a temperature range of -40 to 70°C. It runs on the Linux operating system and comes with an open Edgelink SDK, allowing system integrators to develop customized applications that precisely meet their requirements.

Specifications

General

- **Certification** CE, FCC
- **Mounting** Wall-Mount/ DIN-Rail
- **Power Consumption** 2.4W @ 24V_{DC}
- **Power Requirements** 10 ~ 30 V_{DC}
- **Dimensions (W x D x H)** 30 x 140 x 96.5mm
- **Enclosure** SGCC
- **Operating System** Yocto 4.4

System

- **CPU** Cortex-A35 Quad Core, 1GHz
- **Memory** DDR3L 2GB
- **Indicators** LEDs for Power, LAN (LINK, ACT), Serial (Tx, Rx), Programmable
- **Storage** 16GB eMMC
- **SD Slot** 1 x Micro-SD slot
- **Watchdog** Yes
- **Real-time clock** Yes

Communication

- **Serial Port** 3 x RS-232/485
- **Isolation** 3000 V_{DC}
- **Serial Port Speed** RS-232/RS-485: 50 ~ 115200 bps
- **Ethernet Port** 2 x 10/100 RJ-45 ports
- **Wireless (Optional)** Interface: 1 x Mini-PCIe (Full-size)
Type: WIFI/Cellular/4G
Signal: USB
- **CAN** 1 x CAN (2 pin)

WISE-Edgelink*

- **Protocol Support** OPC-UA Client & Server, BACNet/IP Client & Server, Modbus RTU/TCP, IEC-60870-5-101, IEC-60870-5-103, IEC-60870-5-104
- **PLC Driver Support** Siemens/Mitsubishi/Omron/Allen-Bradley, Delta etc 200+ PLC drivers
- **Programming Support** Linux C, Python
- **Configuration Tool** WISE-EdgeLink Studio
- **Data Monitoring** 20000 Tags Max.
- **Cloud Connectivity** EdgeHub, MQTT, AWS, Azure, LwM2M, Google Cloud IoT Core and more
- **Database Transmission** SQL Server, MySQL, ORACEL, FTP Server
- **VPN** Open VPN


* Edgelink is bundled with Yocto Linux version. Please refer to Edgelink specification for more details.

Environment

- **Operating Temperature** -40~70°C
- **Storage Temperature** -40~85°C
- **Humidity** 5 ~ 95% (non-condensing)

Dimensions

Unit: mm



Ordering Information

Part Number	CPU	RAM	eMMC	OS	Configuration Tool	LAN	COM	CAN	Console
ECU-1260-351A	Cortex-A35 Quad Core, 1GHz	DDR3L 2GB	16GB	Yocto	WISE-EdgeLink	2	3	1	3-pin COM on board

Optional Accessories

Wi-Fi Solution

- **96PD-RYUW131** 2.4GHz Wi-Fi Full/Half Size Mini PCIe Card
- **1750006043** SMA(M) cable, 15 cm
- **1750000318** 2dBi antenna for testing, 11 cm

Cellular Solution (SIM card is not included)

- **96PD-EC25EFA** LTE Cat 4 Module with GNSS
- **1750006264** SMA(F) Cable, 15 cm
- **1750005865** Dipole Antenna, 11 cm

Storage Solution

- **96FMMSDI-4G-ET-AT1** ATP 4G MICRO SD CARD I-GRD SLC(G)
- **96FMMSDI-8G-ET-AT1** ATP 8G MICRO SD CARD I-GRD SLC(G)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[ECU-1260-351A](#)