

# WebOP-3070T

## 7" WVGA Operator Panel with ARM® Cortex™-A8 RISC Processor and Wide Operating Temperature



### Features

- ARM® Cortex™-A8 32-bit, 600 MHz, RISC processor
- Available with a variety of LCD sizes (7/10.1/12")
- TFT LCD with 50K lifetime and LED backlight
- Embedded Microsoft® WinCE 6.0 OS
- Supports Advantech's WebOP Designer HMI Runtime development tool
- 128 KB (64 words) Backup memory FRAM without battery concerns
- Isolation protection for power and terminal I/O ports
- Wide operating temperature range -20 ~ 60 °C (-4 ~ 140 °F)
- Supports the CANopen library defined by the CiA 301 V4.02 specification
- RS-422, RS-485, CAN terminal I/O ports support terminating resistor value of 120Ω
- IP66-rated front panel
- Die cast aluminum alloy front bezel
- Level 4 ESD protection (Air: 15KV/Contact: 8KV)
- UL 508 certification for industrial control equipment



### Introduction

The WebOP-3070T operator panel is powered by an ARM® Cortex™-A8 32-bit, 600 MHz, RISC processor that consumes minimal power without sacrificing performance and satisfies the stringent standards set for the automation market. Additionally, the WebOP-3070T system can be equipped with a variety of LCD sizes, ranging from 7 to 12", for diverse applications that involve PLCs, motion/thermal controllers, inverters, and sensors. Furthermore, the WebOP-3070T system supports a wide operating temperature range (-20 ~ 60 °C/-4 ~ 140 °F) to ensure reliable operation in harsh industrial environments.

### Specifications

#### General

- Certification** CE, BSMI, CCC, UL, FCC Class A
- Dimensions (W x H x D)** 203.4 x 150 x 43.7 mm (8.01 x 5.91 x 1.72 in)
- Cutout Dimensions** 192 x 138.5 mm (7.56 x 5.45 in)
- OS Support** Microsoft® Windows CE 6.0
- Power Input** 24V<sub>DC</sub> ±10%
- Power Consumption** 7W (Typical)
- Enclosure Housing** PC + ABS
- Mounting** Panel
- Weight (Net)** 1 kg (2.20 lbs)

#### System Hardware

- CPU** ARM® Cortex™-A8 32-bit, 600 MHz, RISC processor
- Backup Memory** FRAM 128KB
- Memory** DDR2 256MB on board
- Storage** 512MB on board SLC type
- Power-On LED** Yes

#### Communication Interface

- COM1** RS-232/422/485 (DB9 Male)
- COM2** RS-422/485 (Terminal Plug 4-Pin)
- COM3** RS-485 (Terminal Plug 2-Pin)
- CAN** Terminal Plug 2-Pin
- Ethernet (RJ45)** 10/100BASE-T
- I/Os** 1 x USB 2.0 (Client)  
1 x USB 2.0 (Host)  
1 x micro SD slot  
1 x Audio line out, 1 x mic in

#### LCD Display

- Display Type** WVGA TFT LCD
- Display Size** 7"
- Max. Resolution** 800 x 480
- Max. Colors** 64K
- Luminance (cd/m<sup>2</sup>)** 500

- Viewing Angle (H/V)** 140/120
- Backlight Life** LED, 50,000 hr
- Dimming** Adjustable by touch panel
- Contrast Ratio** 700:1


#### Touchscreen

- Lifespan** 36 million touches of 8 mm in diameter through silicone rubber with at least 250 g load
- Light** Transmission above 80%
- Resolution** Linearity
- Type** 5-wire, analog resistive

#### Environment


- Operating Temperature** -20 ~ 60 °C (-4 ~ 140 °F)
- Storage Temperature** -30 ~ 70 °C (-22 ~ 158 °F)
- Humidity** 10 ~ 90% RH @ 40 °C, non-condensing
- Ingress Protection** Front panel: IP66
- Vibration Protection** Operating, random vibration 1 Grms (5 ~ 500 Hz)

### Base View



## Dimensions

Unit: mm



**Panel Cutout Dimensions: 192 x 138.5 mm (7.56 x 5.45 in)**

## Ordering Information

- WOP-3070T-C4BE 7" WVGA, Cortex™-A8, 256MB DDR, WinCE 6.0

## Optional Accessories

- PWR-247-CE 24 V 60 W AC-DC Power Adapter
- 1702002600 Power Cable US Plug 1.8 M
- 1702002605 Power Cable EU Plug 1.8 M
- 1702031801 Power Cable UK Plug 1.8 M
- 1702031836 Power Cable China/Australia Plug 1.8 M

## S/W Bundle Offering


- WA-HT3070T-R15H0AE WOP-3070T-C4BE with WebAccess/HMI Runtime

## Application Software

### WebAccess/HMI

Advantech WebAccess/HMI is human-machine interface (HMI) software based on Microsoft's Windows operating system. This software features excellent communication and monitoring capabilities, supports more than 350 PLC communication protocols, and offers a wide choice of screen design objects to satisfy diverse integrations of factory automation and HMI operation and monitoring requirements.

## Rear View



Isolated terminal I/O ports

Please note: If some optional modules are offered with the system, additional system certificates may be required in certain regions/countries. Please contact Advantech for certificate compliance.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[WOP-3070T-C4BE](#)