

## Specification Sheet

Part Number: RT150LEP0X2



Special design with extended pawl offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.

Releasable Cable Tie, Release Tab, 32.3" Long, 175lb Tensile Strength, PA66, Black, 25/pkg

Article Number 115-00038

Type RT150LEP

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton heavy duty releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Releasable Cable Tie, Release Tab, 32.3" Long, 175lb Tensile Strength, PA66, Black, 25/pkg

Global Part Name	RT150LEP-PA66-BK
Minimum Tensile Strength (Imperial)	175
Minimum Tensile Strength (Metric)	780
Length L (Imperial)	32.3
Length L (Metric)	820.0
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.35
Width W (Metric)	8.8
Bundle Diameter Min (Imperial)	0.31
Bundle Diameter Min (Metric)	8.0
Bundle Diameter Max (Imperial)	9.65
Bundle Diameter Max (Metric)	245.0

Cable Tie Width Max (Imperial)	0.346
Cable Tie Width Max (Metric)	8.8
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[RT150LEP0X2](#)