



Intel® Core™ i3-13100E Processor

12M Cache, up to 4.40 GHz

Ordering Code

CM8071505110405

Spec Code

SRMFR

Intel® Core™ i3-13100E Processor (12M Cache- up to 4.40 GHz)	
Essentials	
Product Collection	13th Generation Intel® Core™ i3 Processors
Code Name	Products formerly Raptor Lake
Vertical Segment	Embedded
Processor Number	i3-13100E
Lithography	Intel 7
Recommended Customer Price	\$137.00
Use Conditions	Embedded Broad Market Commercial Temp
CPU Specifications	
Total Cores	4
# of Performance-cores	4
# of Efficient-cores	0
Total Threads	8
Max Turbo Frequency	4.40 GHz
Performance-core Max Turbo Frequency	4.40 GHz
Performance-core Base Frequency	3.30 GHz
Processor Base Frequency	3.30 GHz
Cache	12 MB Intel® Smart Cache
Total L2 Cache	5 MB
Processor Base Power	65 W
TDP	60 W
Supplemental Information	

Marketing Status	Launched
Launch Date	Q1'23
Embedded Options Available	Yes
Memory Specifications	
Max Memory Size (dependent on memory type)	128 GB
Memory Types	Up to DDR5 4800 MT/s Up to DDR4 3200 MT/s
Max # of Memory Channels	2
Max Memory Bandwidth	76.8 GB/s
ECC Memory Supported ⓘ	Yes
Processor Graphics	
Processor Graphics ⓘ	Intel® UHD Graphics 730
Graphics Base Frequency	300 MHz
Graphics Max Dynamic Frequency	1.50 GHz
Graphics Output	eDP 1.4b DP 1.4a HDMI 2.1
Execution Units	24
Max Resolution (HDMI)ⓘ	4096 x 2160 @ 60Hz
Max Resolution (DP)ⓘ	7680 x 4320 @ 60Hz
Max Resolution (eDP - Integrated Flat Panel)ⓘ	5120 x 3200 @ 120Hz
DirectX* Support	12
OpenGL* Support	4.5
OpenCL* Support	3
Multi-Format Codec Engines	1
Intel® Quick Sync Video	Yes
Intel® Clear Video HD Technology	Yes
# of Displays Supported ⓘ	4
Device ID	0x4692
Expansion Options	
Direct Media Interface (DMI) Revision	4
Max # of DMI Lanes	8
Scalability	1S Only
PCI Express Revision	5.0 and 4.0

PCI Express Configurations ‡	Up to 1x16+4 2x8+4
Max # of PCI Express Lanes	20
Package Specifications	
Sockets Supported	FCLGA1700
Max CPU Configuration	1
Thermal Solution Specification	PCG 2020C
TJUNCTION	100°C
Package Size	45.0 mm x 37.5 mm
Advanced Technologies	
Intel® Time Coordinated Computing (Intel® TCC)‡	Yes
Intel® Gaussian & Neural Accelerator	3
Intel® Deep Learning Boost (Intel® DL Boost)	Yes
Intel® Speed Shift Technology	Yes
Intel® Turbo Boost Max Technology 3.0 ‡	No
Intel® Turbo Boost Technology ‡	2
Intel® Hyper-Threading Technology ‡	Yes
Intel® 64 ‡	Yes
Instruction Set	64-bit
Instruction Set Extensions	Intel® SSE4.1 Intel® SSE4.2 Intel® AVX2
Idle States	Yes
Enhanced Intel SpeedStep® Technology	Yes
Thermal Monitoring Technologies	Yes
Intel® Volume Management Device (VMD)	Yes
Security & Reliability	
Intel® Standard Manageability (ISM) ‡	Yes
Intel® Control-Flow Enforcement Technology	Yes
Intel® AES New Instructions	Yes
Secure Key	Yes
Intel® OS Guard	Yes
Execute Disable Bit ‡	Yes

Intel® Boot Guard	Yes
Mode-based Execute Control (MBEC)	Yes
Intel® Virtualization Technology (VT-x) ‡	Yes
Intel® Virtualization Technology for Directed I/O (VT-d) ‡	Yes
Intel® VT-x with Extended Page Tables (EPT) ‡	Yes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96MPI-13100E-4E](#)