

Specification Sheet

Part Number: 151-02570



Integrated design allows for easy insertion by hand

0.75–1.25 mm panel thickness range allows for multiple applications

Double-compression design that accommodates various sizes of wire and cable

Presents a high extraction force for withstanding extreme conditions

Low Profile 90° Metal Edge Clip, 0.76–1.24mm Panel Thickness, 4–7.4mm Cable Range, SS304, 5000/box

Article Number 151-02570

Type MSC901

Color Metal (ML)

Quantity Per box

Product Description HellermannTyton's Metal Edge Clip provides an excellent alternative to managing wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Metal Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. The Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.

Short Description Low Profile 90° Metal Edge Clip, 0.76–1.24mm Panel Thickness, 4–7.4mm Cable Range, SS304, 5000/box

Global Part Name MSC901-SS304-ML

Length L (Imperial) 0.73

Length L (Metric) 18.44

Width W (Imperial) 0.460

Width W (Metric) 11.57

Bundle Diameter Min (Imperial) 0.161

Bundle Diameter Min (Metric) 4.1

Bundle Diameter Max (Imperial) 0.291

Bundle Diameter Max (Metric) 7.39

Panel Thickness Min (Imperial) 0.03

Panel Thickness Max (Imperial) 0.049

Panel Thickness Min (Metric) 0.76

Panel Thickness Max (Metric) 1.24

Material Stainless Steel (SS304)

Material Shortcut	SS304
Flammability	Non-burning
Halogen Free	No
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	5000 pieces
Package Quantity (Metric)	5000
Customs Number	7326908695

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-02570](#)