






Assembled example isometric view




Assembled example front view



2X(Ø17)



Delivery condition



- Notes:
1. Material: See chart
 2. Material color: See chart
 3. Maximum percent regrind permissible: 0%
 4. Max allowable flash to be: 0.50mm
 5. Max allowable mismatch to be: 0.1mm
 6. Threaded stud length to be at least: 40mm
 7. Applicable stud size:
A. M8 x 1.25 Threaded



Global Part Description	Housing		
	Drawing	Material	Color
HDC17X2-PA66GF15/TPE-BK	21-0307-005-CSU	PA66GF15/TPE	Black

Revision Level			Revision Record			The copyright of this drawing is reserved by HellermannTyton.	Drawn	Date (YYYY/MM/DD)	Title			Scale
Drawing	State	Part	ECN 310292				Rohde	2021/09/02				1:1
03.1	Design Release				Approved		Date (YYYY/MM/DD)	Global Project Number				
Changed	Date (YYYY/MM/DD)				Haftarski		2022/01/14	21-0307				
Rohde	2023/09/12		All drawing revisions are stored in CAD PDM database		Units mm	HellermannTyton	www.HellermannTyton.com	Drawing-No	21-0307-105-CSU	Format		
Approved	Date (YYYY/MM/DD)									A3		
Van Hulst	2023/09/13									Sheet		
										1 / 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-04059](#)