











- Reference:
- Performance requirements at dry as molded:
1. Fir tree push in force: 45 newtons (10 lbf) max in the applicable nominal hole size and a plate thickness of 1.8mm.
 2. Fir tree pull out force: 110 newtons (25 lbf) min in the applicable nominal hole size and a plate thickness of 1.8mm.

- Notes:
1. Material: See chart
 2. Material color: See chart
 3. Maximum percent regrind permissible: 25%
 4. Max allowable flash to be: 0.5mm
 5. Max allowable mismatch to be: 0.1mm
 6. Sheet metal thickness range: 0.60mm - 6.00mm
 7. Applicable hole size:
A. 6.5mm +0.5/- 0.4

Global Part Description	Material	Color
ROC18.5-22.5FT6.5-PA66HIRHSUV-BK	PA66HIRHSUV	Black

Revision Level		
Drawing	State	Part
00.0	Design Release	-
Changed	Date (YYYY/MM/DD)	
Karabon	2024/03/22	
Approved	Date (YYYY/MM/DD)	
Van Hulst	2024/03/22	

Revision Record	
ECN 311027	

All drawing revisions are stored in CAD PDM database

The copyright of this drawing is reserved by HellermannTyton.

Drawn	Date (YYYY/MM/DD)
Karabon	2024/03/22
Approved	Date (YYYY/MM/DD)
Van Hulst	2024/03/22

Title	Ratchet O-Clamp, 18.5-22.5mm, with 6.5mm fir tree	
	Scale 1:1	
	Global Project Number 24-0946	
Drawing-No		Format A3
24-0946-001-CSU		Sheet 1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-04403](#) [151-04351](#)