

Specification Sheet

Part Number: RJ45FC6-VIO


Category 6 jack has been uniquely designed adopting HellermannTyton's globally tried and tested 10-Pin technology which guarantees superior performance and connectivity

Standard keystone style interface provides flexibility in connecting components

Unique strain relief design secures cable terminations

Configured to both TIA 568A and 568B wiring schemes for installation versatility

Suitable for air handling spaces, ideal for installation of WAPs and IP devices



Category 6 Modular Keystone Jack, Plenum Rated, Violet, 1/pkg

Article Number	852-25080
Type	RJ45FC6-VIO
Color	Violet (VT)
Quantity Per	bag

Product Description	HellermannTyton's GigaBand flush Category 6 modular jack is designed to “future-proof” installations. Its patented design uses innovative crosstalk-cancellation technology. The performance of the GigaBand system provides significant margin over TIA Category 6 (ANSI/TIA-568-C.1) and ISO Class E (ISO/IEC-11801, 2nd edition) requirements. The GigaBand system will easily support applications such as Gigabit Ethernet. ETL tested and approved for Category 6 component compliance.
Short Description	Category 6 Modular Keystone Jack, Plenum Rated, Violet, 1/pkg
Global Part Name	RJ45FC6-VIO
Technical Description	The performance of the Cat6 system provides significant margin over TIA Cat6 and ISO/IEC 11801 requirements.
Port Count	1
Width W (Imperial)	9.75
Width W (Metric)	19.0
Height H (Imperial)	9.91
Height H (Metric)	23.0
Depth D (Imperial)	1.65
Depth D (Metric)	42.0
UL Listed (US and Canada)	Yes

UL Listed (US)	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8536695050
Weight (Metric)	0.010

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[RJ45FC6-VIO](#)