

Specification Sheet

Part Number: GSTAPP-1U24SC

Unshielded 24 ports

Angled 1U presentation

Screen printed labelling fields & port numbers

Accepts HT Connectivity unshielded keystone jacks

Optional cable management



GST Angled Modular Patch Panel 24 Port, 1U, Steel, Black, 1/box

Article Number	853-50051
Type	GSTAPP-1U24SC
Color	Black (BK)
Quantity Per	box

Product Description	The HellermannTyton range of Modular Keystone panels offer exceptional flexibility and performance in an angled or flat format in 2U 48 port, 2U 72 port, 1U 48 port and 1U 24 port configurations. The Modular Keystone panels offer industry standard apertures and are compatible with the HellermannTyton range of keystone jacks. The use of individual keystone jacks offers a balanced system performance and also provides simple installation and maintenance allowing individual jack to be removed if required. The angled presentation increases rack capacity by allowing patchcords to be directed to the vertical cable management and aids correct cable bend radius. Optional rear cable manager is also available and is sold separately.
Short Description	GST Angled Modular Patch Panel 24 Port, 1U, Steel, Black, 1/box
Global Part Name	GSTAPP-1U24SC
Technical Description	The Angled Modular Keystone panel is manufactured from 1.6mm powder coated mild steel making it rigid and robust. The panel has a matteblack powder coated finish and is screen printed with port numbers as well as clear port identification labelling areas for easy user identification. Each U also has a central labelling field for panel identification.
Port Count	24
Width W (Imperial)	19.02
Width W (Metric)	483
Height H (Imperial)	1.73
Height H (Metric)	44
Depth D (Imperial)	4.17

Depth D (Metric) 106

UL Listed (US and Canada) Yes

UL Listed (US) Yes

Package Quantity (Imperial) 1

Package Quantity (Metric) 1

Customs Number 9030400000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[GSTAPP-1U24SC](#)