


Specification Sheet

Part Number: MDUS5-LL1SP



High fiber splice capacity to accommodate large MDUs or be used as a Building Entry Point (BEP).

UV stable enclosure with IP54 (NEMA 3S) sealing and IK08 impact rating for long-term outdoor performance.

Supports cabled, blown, pushed and pulled fiber deployments to accommodate any construction style.

S5 Splice Enclosure, 216 Fiber Splice, Wall Mounted, Gray, 1/pkg

Article Number	857-01494
Type	MDU-S5-LLWX
Color	Gray RAL 7035 (7035)
Quantity Per	EA

Product Description

The large S5 enclosure is designed for wall-mount distribution, configured with the HellermannTyton IR Management System. The management system accommodates 9x 900µm trays or 18x 250µm trays, for a maximum of 144x 900µm heat shrink splices or 288x 250µm heat shrink splices. The position of the fiber management system allows easy access for the routing of fiber on to the trays. The trays and fiber-optic routing modules are white, making it easy to see the color of the fiber elements as they are routed through the positive fiber management system. Fiber slot retaining blocks guide the fiber elements on to the IR system; the foam pad on the retainer is partially cut through to accommodate a range of fiber counts. A loop storage basket provides space for the storage of fiber loops. Designed with eight dual input/output ports; four across the bottom, two on top and two on each side; each port will accommodate a 20 or 25 mm cable gland.

Short Description

S5 Splice Enclosure, 216 Fiber Splice, Wall Mounted, Gray, 1/pkg

Global Part Name

MDU-S5-LLWX

Technical Description

The S5 enclosure is configured with the HellermannTyton 250µm IR Management System. The management system is mounted on an aluminium backplane which accommodates 18 SE-IR trays giving a maximum of 216 3A fibre splices. The position of the fibre management system allows for easy access for the routing of fibre on to the trays. The trays and fibre optic routing modules are white which makes it easy to see the colour of the fibre elements as they are routed through the positive fibre management system. Fibre slot retaining blocks guide the fibre elements on to the IR system; the foam pad on the retainer is partially cut through to accommodate a range of fibre counts. All IR system cover plates are coloured blue identifying them as removable parts allowing access to the fibre, the fibre retaining block and tray retaining clips are coloured red to aid in identification if they are dropped. Loop storage management for both incoming and outgoing cables is provided by lateral cable managers and loop storage bobbins located on either side of the fibre management trays. The enclosure is 568 x 375 x 165mm (H x W x D) and manufactured in light grey (RAL 7035), UV stable ABS (Acrylonitrile Butadiene Styrene) and has an IP54, IK08 and V0 rating. Designed with 8 dual input/output ports, 4 across the bottom, 2 on the top and 2 on each side, each port will accommodate a 20 or 25mm cable gland. A 100 x 25mm inset position on the front cover allows for a customer logo to be moulded in to the enclosure.

Contents of pkg/kit	S5 Enclosure 250µm IR Fibre Management System 18 SE-IR Trays with 3A Splice Bridges 2 Loop Storage Managers 4 x Entry/Exit Port Blanks Strength Member Anchor In-built spirit level Fibre Picker Wall Mounting Kit Red and Green Polyspiral Tubing(2M) Red and Green Velcro Ties(5)
Port Count	8
Variant	Indoor/Outdoor FTTx Enclosures
Width W (Imperial)	9.72
Width W (Metric)	375
Height H (Imperial)	22.36
Height H (Metric)	568
Depth D (Imperial)	6.50
Depth D (Metric)	165
Material	Acrylonitrile Butadiene Styrene (ABS)
Material Shortcut	ABS
Package Quantity (Imperial)	1

Package Quantity (Metric) 1

Customs Number 9030400000

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[MDUS5-LL1SP](#)