


















TABLE 1				
CABLE GROUP	CABLES ACCOMMODATED	ASSEMBLE PER		"D" MAX
-201	M17/176-00002	TAI-166	1  (1.00) STRAIN RELIEF 1  (1.25) SEALING SLEEVE	1.70
-202	TWC-78-1			
-203	TWC-124-1A			
-204	10602, RAYCHEM			
-205	TWAC-78-1F2			
-206	7826D0130, RAYCHEM			
-207	83310, BELDEN			
-208	202-3927, MICRODOT			
-209	202-3942, MICRODOT			
-210	8451, BLEDEN			
-211	202-3934, MICRODOT	TAI-138	1  (1.75) STRAIN RELIEF	1.44
-212	2524E0114, RAYCHEM			
-213	TWC-78-2			
-214	TWC-124-2			
-215	BL982, TIMES			
-216	BL1242, TIMES	TA-166	1  (1.00) STRAIN RELIEF 1  (1.25) SEALING SLEEVE	1.70
-217	GC875TM24H, GRUMMAN			
-218	EDP22188B, RAYCHEM			
-219	2526D1114, RAYCHEM			
-220	GC875RR1, GRUMMAN			
-221	10614, RAYCHEM			
-222	10613, RAYCHEM			
-223	HMS2-1149, HUGHES			
-224	TWCP-124-3			
-225	PS665PL, PRIME STOCK			
-301	GC875GC1, GRUMMAN	TAI-168	1  (1.00) STRAIN RELIEF 1  (1.25) SEALING SLEEVE	1.70
-302	GC875GB1, GRUMMAN			
-303	7528A5314, RAYCHEM			
-305	M17/177-00001, THERMATICS			
-306	TRC-50-5 M17/134-00002	TAI-218	1  (1.75) STRAIN RELIEF	
-307	TRC-75-1	TAI-168	1  (1.00) STRAIN RELIEF 1  (1.25) SEALING SLEEVE	
-308	TRC-75-2	TAI-218	1  (1.75) STRAIN RELIEF	
-309	TRC-50-1	TAI-168	1  (1.00) STRAIN RELIEF 1  (1.25) SEALING SLEEVE	

TABLE 2			
POLARIZATION CHART			
KEYING LETTER	"A"° ±1°	"B"° ±1°	"C"° ±1°
NONE	120	120	120
T	100	150	110
U	120	130	110
V	115	130	115
W	125	110	125
X	130	100	130
Y	110	140	110
Z	100	160	100
S	135	135	90



5-0011T-201 SHOWN



5-0011-201 SHOWN

NOTES: UNLESS OTHERWISE SPECIFIED.

- MATERIAL & FINISH:
  - 1.1 BODY: NICKEL PLATED BERYLLIUM COPPER
  - 1.2 BAYONET SLEEVE & CRIMP BUSHING: NICKEL PLATED BRASS
  - 1.3 INSULATOR & DIELECTRIC: PTFE (TEFLON)
  - 1.4 INTERMEDIATE CONTACT: GOLD PLATED BERYLLIUM COPPER
  - 1.5 CENTER CONTACT: GOLD PLATED BRASS
  - 1.6 GASKET: SILICONE RUBBER

- ELECTRICAL:
  - 2.1 FREQUENCY (MAX): 500 MHZ
  - 2.2 IMPEDANCE: NON-CONSTANT

- EXAMPLE OF COMPLETE MODEL NUMBER:

5-0011 A -XXX

└─ KEYING LETTER (SEE TABLE 2)




└─ CABLE GROUP (SEE TABLE 1)

└─ BASE MODEL NUMBER

 SHRINKABLE STRAIN RELIEF AND/OR SEALING SLEEVE SUPPLIED PER TABLE 1.

- TESTED PER TT-09, IAW TCS-70

- WORKMANSHIP PER TFS-10

 <small>This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand.</small> <small>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.</small>	 <b>RoHS2</b>  2015/863/EU <small>UNLESS OTHERWISE SPECIFIED</small> UNITS: INCH .XX ±.02 .XXX ±.010 ANGLES ±2°	<b>TROMPETER</b>		
		Title: TRB CABLE PLUG, TOOL CRIMP SPACE RATED		
		Model No. 5-0011A-XXX		
		Size B	DO NOT SCALE DRAWING	Date 7/8/2019 Sheet 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[5-0011-201](#)