

Specification Sheet

Part Number: VFA2LCLCOM1

Pre-radiused zirconia ceramic ferrules for precision alignment.
Industry standard ST, SC, MTRJ or LC connectors to suit specific applications.


Available in 1-5 meter lengths for a variety of applications.

Color coded for easy identification.

Individually quality tested for insertion and return loss.

Meet ANSI/TIA/EIA 568-B standards.

Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.



FT LC - LC Duplex OM1 Fiber Assembly, 2M, Orange, 1/pkg

Article Number	904-00552
Type	VFA2LCLCOM1
Color	Orange (OG)

Product Description	For fiber patching requirements, HellermannTyton offers fiber optic jumpers in various lengths with a wide variety of connector configurations. HellermannTyton offers fiber jumpers in two types – standard and high performance. Our standard jumpers combine quality with value. They meet all ANSI/TIA/EIA fiber optic cable requirements while allowing installers to maximize project budgets. In addition to meeting industry standards, HellermannTyton high performance jumpers have additional features designed for high performance applications . Our high performance jumpers meet Trade Agreement Act (TAA) requirements, making them suitable for use in General Services Administration (GSA) government contract projects.
Short Description	FT LC - LC Duplex OM1 Fiber Assembly, 2M, Orange, 1/pkg
Global Part Name	VFA2LCLCOM1-Glass/PVC/PL-OG
Technical Description	FT LC - LC Duplex OM1 Fiber Assembly, 2M, Orange
Length L (Imperial)	6.6
Length L (Metric)	2.0
Material	Glass (Glass) Polyvinylchloride (PVC) Plastic (PL)
Material Shortcut	PVC PL Glass
Package Quantity (Imperial)	1
Package Quantity (Metric)	1

Customs Number

8544700000

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[VFA2LCLCOM1](#)