

## Specification Sheet

Part Number: 111-02387



Engineered and manufactured for maximum performance and quality  
Made from 100% high-quality plastic to ensure efficient recycling

Inside serration for a strong grip onto bundles

Easy application either manually or with a processing tool

<b>Article Number</b>	111-02387
<b>Type</b>	T150L
<b>Color</b>	Yellow (YE)
<b>Quantity Per</b>	bag
<b>Product Description</b>	Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
<b>Short Description</b>	Heavy Duty Cable Tie, 32" Long, UL Rated, 175lb Tensile Strength, PA66, Yellow, 50/pkg
<b>Global Part Name</b>	T150L-PA66-YE

<b>Minimum Tensile Strength (Imperial)</b>	175.0
<b>Minimum Tensile Strength (Metric)</b>	780.0
<b>Length L (Imperial)</b>	32.0
<b>Length L (Metric)</b>	820.0
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Inside Serrated
<b>Width W (Imperial)</b>	0.35
<b>Width W (Metric)</b>	8.9
<b>Bundle Diameter Min (Imperial)</b>	0.31
<b>Bundle Diameter Min (Metric)</b>	8.0
<b>Bundle Diameter Max (Imperial)</b>	9.65
<b>Bundle Diameter Max (Metric)</b>	245.0
<b>Thickness T (Metric)</b>	1.9

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V-2
<b>Halogen Free</b>	Yes
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Compliant</b>	Yes
<b>UL Recognized (US)</b>	Yes
<b>UL Listed (US and Canada)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity (Imperial)</b>	50
<b>Package Quantity (Metric)</b>	50
<b>Customs Number</b>	3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[111-02387](#)