

Specification Sheet

Part Number: 111-12076



- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail allows for simpler insertion.
- Complies with MS3367-3-9, Class 1 and SAE-AS33671.

Heavy Duty MilSpec Cable Tie, 15" Long, MS3367, 120lb Tensile Strength, PA66, Natural, 500/bg

Article Number	111-12076
Type	T120R
Color	Natural (NA)
Quantity Per	box
Product Description	Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. The bent tail allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation. Specially manufactured to comply with Military Specification MS3367-3-9, Class 1 and SAE-AS33671.

Short Description	Heavy Duty MilSpec Cable Tie, 15" Long, MS3367, 120lb Tensile Strength, PA66, Natural, 500/bg
Global Part Name	T120R-PA66-NA
Minimum Tensile Strength (Imperial)	120.0
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	15.0
Length L (Metric)	387.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.30
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.12
Bundle Diameter Min (Metric)	3.0
Bundle Diameter Max (Imperial)	3.94
Bundle Diameter Max (Metric)	100.0

Thickness T (Imperial)	0.07
Thickness T (Metric)	1.9
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
US MIL SPEC	SAE-AS33671 MS3357-3-9, Class 1
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[111-12076](#)