

Specification Sheet


Part Number: 151-03010

One-piece ratchet closure design allows for easy installation during pre- or final assembly.

Easy release feature allows for quick adjustments and maintenance.

Stainless steel mounting plate tolerates high torque mounting, resists galvanic corrosion with dissimilar metals, and harsh chemicals.

Low fire hazard materials comply with stringent NFPA 130 safety standards and improve opportunities to get product specified at the engineering stage of a project.



Ratchet P-Clamp, 1.38 - 2.01" Bundle Dia, 90° Long, 0.41" Hole Dia, PA666V0/SS304, Black, 140/ctn

Article Number	151-03010
Type	RCD90LM10SS
Color	Black (BK)
Quantity Per	bag

Product Description	The Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This nondestructive release allows the clamp to be reused without removing or replacing any bolts or screws. The Ratchet P-Clamp is offered in four sizes and multiple mounting configurations. Low fire hazard material is designed specifically for rail applications.
Short Description	Ratchet P-Clamp, 1.38 - 2.01" Bundle Dia, 90° Long, 0.41" Hole Dia, PA666V0/SS304, Black, 140/ctn
Global Part Name	RCD90LM10SS-PA666V0/SS304-BK
Minimum Tensile Strength (Imperial)	100.0
Minimum Tensile Strength (Metric)	445.0
Length L (Imperial)	7.69
Length L (Metric)	195.2
Fixation Method	Screw Mounting
Variant	Long
Width W (Imperial)	1.37
Width W (Metric)	34.9
Bundle Diameter Min (Imperial)	1.42

Bundle Diameter Min (Metric)	36.0
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	51.0
Mounting Hole Diameter D (Imperial)	0.41
Mounting Hole Diameter D (Metric)	10.4 mm
Stud Diameter (Metric)	M10
Mounting Hole Centers (Imperial)	3.72
Material	Polyamide 6.6 + Polyamide 6 V0 (PA66/6V0) Stainless Steel (SS304)
Material Shortcut	SS304 PA666V0
Flammability	UL 94 V-0 Halogen-free Low generation of toxic gases and corrosive acid Low smoke generation Limited fire hazard
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Certification/Specification

ASTM 1354 ASTM E 162 ASTM E 662 EN [45545-2]

Package Quantity (Imperial)

140

Package Quantity (Metric)

140

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-03010](#)