



Technical Data Sheet

Rosenberger

MCX

Termination
Plug 1 Watt

29S15R-1.0E3



All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to

IEC 61169-36

Documents

N/A

Material and plating

Connector parts

Center conductor
Outer conductor
Dielectric
Substrate

Material

Brass
Beryllium copper
PTFE, Silicone
Al₂O₃

Plating

Gold, min. 1.27 µm, over nickel
Gold, min. 0.8 µm, over nickel

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/09.14/6.2

Technical Data Sheet				Rosenberger			
MCX		Termination Plug 1 Watt		29S15R-1.0E3			
Electrical data Impedance50 Ω FrequencyDC to 6 GHz Return loss≥ 23.1 dB, DC to 4 GHz ≥ 17.7 dB, 4 GHz to 6 GHz Power handling (at 25 °C, sea level)1 W at 2.5 GHz, derated linearity by 0.01 W/K Mechanical data Mating cycles≥ 500 Center contact captivation≥ 10 N Engagement force≤ 25 N Disengagement force8 N to 20 N Environmental data Temperature range-55 °C to +155 °C RoHScompliant Tooling N/A Suitable cables N/A Packing Standard100 pcs in bag Weight0.7 g/pce							
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Kerstin Herzog	16.02.05	Markus Müller	22.05.18	b00	18-1027	Marion Striegler	22.05.18
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de			Page 2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[29S15R-1.0E3](#)