



All dimensions are in mm

Component

Powersystem Port 12V for use with

Magcode Powersystem Clip 24V
Magcode spring loaded cover

M2K212-1AE
M2Z101-3XX

Documents

Assembly instruction
Handling instruction
Panel piercing

MA_M2V001
HI_005
MB_612

Material and plating

Connector parts

Housing
Spacer (2x)
Nut
Contact surface (interface)
Contact surface (cable outlet)

Material	Plating
PBT ASA GF20	none
PBT ASA GF20	none
PBT ASA GF20	none
Cu / AgNi	none
Cu / AgNi	none

Preliminary

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF_35/09.14/6.2



Electrical data

Connection Technology	6,3 mm flat connector tin plated
Rated voltage	24 V DC
Max current load	15 A at 60° C

Mechanical data

Locking mechanism	magnetic
Mounting cut-out	∅ 28 mm (M28)
Duty cycles without load	> 10.000 cycles
Duty cycles at 15 A	4.000 cycles
Vibration resistance	3 axes, 8h, 5Hz-200Hz, 8,5 m/s ²
Shock resistance	3 axes, 13.000 shocks, 11 ms. 30g

Environmental data

Temperature range	-40° C to +105° C
Dust and water resistance (interface)	IP6K9K
Dust and water resistance (cable outlet)	IP5K0
RoHS	compliant

Packing

Standard	bulk
Weight	29,5 g/pce

Preliminary

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
J. Hegenauer	14.04.16	C. Biermann	10.11.21	300	21-2086	S. Höglauer	10.11.21

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[M2S112-3XX](#)