

Specification Sheet

Part Number: 553-60038



Halogen free, for low smoke propagation, density and toxicity.
50 mm, 25 mm and 16 mm pre-cut marker options as standard, for ability to get multiple labels out of one tag.

Delivery in convenient storage boxes for protection.

ShrinkTrak Labels, 2-Sided, 2-Slit, Halogen Free, 0.63" x .20", Polyolefin, White, 15,000/pkg

Article Number	553-60038
Type	TLFX24DS-3x16WH
Color	White (WH)
Quantity Per	pack

Product Description	ShrinkTrak DS is a halogen-free, double-sided heat shrinkable marker with a 2:1 shrink ratio. HellermannTyton's unique ladder-style design assists in removing markers off the carrier. The side slits have been designed to ensure the wire entry gap is as large as possible while remaining on the carrier strip, enabling the user to quickly insert wire and cable into the marker. For a complete labeling solution, ShrinkTrak DS can be printed using HellermannTyton's TagPrint® Pro professional label creation software and thermal transfer printers. For double-sided printing, HellermannTyton's TrakMark DS double-sided printer produces excellent results. Choose among multiple ribbon types to create a permanent print that resists most solvents when shrunk and applied.
Short Description	ShrinkTrak Labels, 2-Sided, 2-Slit, Halogen Free, 0.63" x .20", Polyolefin, White, 15,000/pkg
Global Part Name	TLFX24DS-3x16WH-PO-X-WH
Length L (Imperial)	0.63
Length L (Metric)	16.0
Fixation Method	Others
Variant	Thin-Wall
Width W (Imperial)	0.63
Width W (Metric)	16.0
Thickness T (Imperial)	.0130
Thickness T (Metric)	.29
Height H (Imperial)	0.19

Height H (Metric)	5.0
Width of Liner (Metric)	88.9
Width of Liner (Imperial)	3.50
Outside Diameter Max (Imperial)	0.09
Outside Diameter Max (Metric)	2.28
Wall Thickness WT (Imperial)	0.020
Wall Thickness WT (Metric)	0.515
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	MIL-STD-202J SAE AS5942 3.4.1
Flammability	Low smoke generation UL 224 Limited fire hazard Low generation of toxic gases and corrosive acid Halogen-free
Halogen Free	Yes
Operating Temperature	-67°F to +221°F (-55°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Certification/Specification	DIN EN [45545-2] ASTM E 662 ASTM 1354 ASTM E 162
Package Quantity (Imperial)	15000
Package Quantity (Metric)	15000
Customs Number	3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[553-60038](#)