

## Specification Sheet

Part Number: VFA6LCLCOS2

Pre-radiused zirconia ceramic ferrules for precision alignment.  
Industry standard ST, SC, MTRJ or LC connectors to suit specific applications.


Available in 1-5 meter lengths for a variety of applications.

Color coded for easy identification.

Individually quality tested for insertion and return loss.

Meet ANSI/TIA/EIA 568-B standards.

Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.



FT LC - LC Duplex OS2 Fiber Assembly, 6M, Yellow, 1/pkg

<b>Article Number</b>	904-00850
<b>Type</b>	VFA6LCLCOS2
<b>Color</b>	Yellow (YE)
<b>Quantity Per</b>	box

<b>Product Description</b>	For fiber patching requirements, HellermannTyton offers fiber optic jumpers in various lengths with a wide variety of connector configurations. HellermannTyton offers fiber jumpers in two types—standard and high performance. Our standard jumpers combine quality with value. They meet all ANSI/TIA/EIA fiber optic cable requirements while allowing installers to maximize project budgets. In addition to meeting industry standards, HellermannTyton high-performance jumpers have additional features designed for high performance applications. Our high-performance jumpers meet Trade Agreement Act (TAA) requirements, making them suitable for use in General Services Administration (GSA) government contract projects.
<b>Short Description</b>	FT LC - LC Duplex OS2 Fiber Assembly, 6M, Yellow, 1/pkg
<b>Global Part Name</b>	VFA6LCLCOS2-GF-YE
<b>Technical Description</b>	FT LC - LC Duplex OS2 Fiber Assembly, 6M, Yellow
<b>Length L (Imperial)</b>	19.7
<b>Length L (Metric)</b>	6.0
<b>Material</b>	Glass Fiber (GF)
<b>Material Shortcut</b>	GF
<b>Package Quantity (Imperial)</b>	1
<b>Package Quantity (Metric)</b>	1

**Customs Number** 8544700000

**Weight (Metric)** 680.4

**Weight (Imperial)** 1.5

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[VFA6LCLCOS2](#)