

UPD78F1505AGC-UEU-AX

User's Manual: Hardware

Overview

Design Support

Documentation

Sample Code

Software & Tools

Ordering

PARAMETRICS

Parameters	UPD78F1505AGC-UEU-AX
Package	
Pin Count	100
Package Type	LFQFP
Memory	
Program memory	128 KB Flash memory
RAM	7 KB
CPU (Bit, Clock, DMA, External Bus etc)	
CPU	78K0R (16-bit)
Max. Frequency	20 MHz
Sub-Clock (32.768 kHz)	YES
On-chip Oscillator Freq.	20, 8, 1 MHz
Power-On Reset	YES
Low Voltage Detection	YES
DMA Remarks	DMAC x 2 ch
External Interrupt Pins	12
I/O Ports	65
Timers	
16-bit Timers	12 ch
Watchdog Timers	1 ch
PWM Output	7
Analog	
A/D Converters	12-bit x 12 ch
D/A Converters	12-bit x 2 ch
Interfaces	
CSIs	3 ch
UARTs	4 ch
I2Cs	3 ch
LIN	1 ch
Display Functions	
LCD Remarks	seg=36, com=8
Operating Conditions	
Operating Voltage	1.8 to 5.5 V
Operating Temperature	-40 to 85 °C (Ambient Temperature)
Remarks	
Remarks	100-pin 16-bit single-chip microcontroller (78K0R/LG3)

[View Less](#)

Need More Help?

Contact Us Website Feedback

Forums Videos

Knowledgebase

About Renesas

News

Investors

Careers

Follow Us

Facebook YouTube

Twitter LinkedIn

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Renesas Electronics:](#)

[UPD78F1505AGC-UEU-AX](#)