

PART NO. : HFJT1-1G04RL



FASTJACK™ (TABUP) WITH 1000BASE-T MAGNETICS
 DESIGNED FOR IEEE802.3ab GIGABIT APPLICATIONS

RoHS COMPLIANT


COMPATIBLE TO LEAD-FREE WAVE SOLDERING PROCESS
 FOR THROUGH HOLE COMPONENTS

OPERATING TEMPERATURE 0/70°C




ELECTRICAL SPECIFICATIONS @ 25° C

URNS RATIO	1:1 ±3%
OCL (100KHz,0.1V,8mA)	350µH min
INSERTION LOSS	
1-100MHz	-1.1dB max
RETURN LOSS	
1-40MHz	-18dB min
60MHz	-14dB min
80MHz	-12dB min
100MHz	-10dB min
CROSSTALK 1-100MHz	-35dB typ
CMR 0.1-30MHz	-50dB typ
30-60MHz	-40dB typ
60-100MHz	-35dB typ
ISOLATION	1,500Vrms

PRELIMINARY



HALO/PBL	TITLE FastJack™ SINGLE		SIGNATURES		DATE	REV.	DESC.	DATE
	FOR GIGABIT ETHERNET		DRAWN LI ZHI ZHONG		4/13/11	A	FIRST ISSUE	4/13/11
	PART NO. HFJT1-1G04RL		CHECKED LEI KEONG		4/15/11	B	REV. MARKING	4/15/11
	SCALE NONE		PAGE 1 OF 2		APPROVED PETER LU	4/15/11		
CALIFORNIA, USA KOWLOON, HONG KONG SINGAPORE		FILE HFJT1-1G04RL.DWG						



Housing Material: Polyester, Black UL94V-0
 Contacts: Phosphor Bronze 30µin Au plating over Ni
 Leads: Matte Sn over Ni
 Shield: Cu Alloy with Ni plating 40µin min
 Durability: 1000 mating cycles
 Dimensions: Inch [mm]
 Tolerances: ±0.008 inch if not specified

RECOMMENDED P.C. BOARD PATTERN (COMP. SIDE)

HALO/PBL	TITLE	FastJack™ SINGLE	SIGNATURES		DATE	REV.	DESC.	DATE
	FOR	GIGABIT ETHERNET	DRAWN	LI ZHI ZHONG	4/13/11	A	FIRST ISSUE	4/13/11
CALIFORNIA, USA KOWLOON, HONG KONG SINGAPORE	PART NO.	HFJT1-1G04RL	CHECKED	LEI KEONG	4/15/11	B	REV. MARKING	4/15/11
	SCALE	NONE	APPROVED	PETER LU	4/15/11			
	PAGE	2 OF 2	FILE	HFJT1-1G04RL.DWG				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HALO Electronics:](#)

[HFJT1-1G04RL](#)