

Customer Part:

Description

- IQXT-205-3-18 is a 2.0 x 1.6mm SMD Temperature Compensated Crystal Oscillator (TCXO) in a hermetically sealed package with a wide operating temperature range.
- Model IQXT-205-3-18
- Model Issue number 1

Frequency Parameters

- Frequency 33.60MHz
- Frequency Tolerance Max ± 1.50 ppm
- Tolerance Condition @ 25°C $\pm 2^\circ$ C
- Frequency Stability ± 0.50 ppm
- Operating Temperature Range -40.00 to 105.00°C
- Ageing ± 1 ppm max per year @ 25°C $\pm 2^\circ$ C
- Frequency Tolerance: Referred to nominal frequency before reflow soldering.
- IR Reflow Resistance (@ 25°C $\pm 2^\circ$ C ref to frequency before reflow): ± 1 ppm max, 24hrs after reflow
- Supply Voltage Variation (@ $\pm 5\%$ change): ± 0.1 ppm max
- Load Variation (@ $\pm 10\%$ change): ± 0.1 ppm max

Electrical Parameters

- Supply Voltage 1.8V $\pm 5\%$
- Current Draw Max 1.700mA
- Absolute Maximum Ratings: Supply Voltage: -0.6V to 4.6V

Output Details

- Output Compatibility Clipped Sine
- Drive Capability 10k Ω //10pF
- Output: DC coupled
- Output Level: 0.8V pk-pk min
- Start Up Time (90% of V pk-pk): 2ms max
- Start Up Time (within ± 0.5 ppm): 2ms max

Noise Parameters

- Phase Noise (typ): -135dBc/Hz @ 1kHz

Environmental Parameters

- Storage Temperature Range: -40 to 105°C

Manufacturing Details


- RoHS Terminations NiAu
- RoHS Reflow Temp $+250^\circ$ C $\pm 10^\circ$ C for 10 sec max

Compliance


- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): 2

Packaging Details

- Pack Style: **Cutt** **Cut tape**
Standard Pack Quantity: 100
- *Alternative packing option available*

Outline (mm)

Pad Connections

1. GND
2. GND
3. Output
4. +Vs

Solder Pad Layout

Sales Office Contact Details:

UK: +44 (0)1460 270200

 Email: info@iqdfrequencyproducts.com

 Web: www.iqdfrequencyproducts.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IQD Frequency Products:](#)

[LFTCXO079060Reel](#)