





8828000G001-055



MECHANICAL SPECIFICATIONS	
DURABILITY	500 MIN
CAPTIVATION - CONTACT	2 LBS MIN



ELECTRICAL SPECIFICATIONS	
FREQUENCY RANGE	DC-40 GHz
VSWR (DC-18 GHz)	1.25:1 MAX
IMPEDANCE	50 ± 2 OHMS
WORKING VOLTAGE @ SEA LEVEL	335 Vrms MIN
DWV @ SEA LEVEL	500 Vrms MIN
INSULATION RESIST.	5,000 MΩ

ENVIRONMENTAL SPECIFICATIONS	
TEMP RANGE	-65° TO +125° C

- NOTES:
- ASSEMBLED CONNECTOR INTERFACE IS DESIGNED IN ACCORDANCE WITH MIL-STD-348.

BODY	BERYLLIUM COPPER PER ASTM B196, C17300, TEMPER TD04	GOLD PLATE PER ASTM B488
CONTACT	BERYLLIUM COPPER PER ASTM B196, C17300, TEMPER TD04	GOLD PLATE PER ASTM B488
INSULATOR	TEFLON PER ASTM D1710, TYPE 1, GRADE 1, CLASS A.	N/A
DESCRIPTION	MATERIAL	FINISH

Table 1

<div>UNLESS OTHERWISE SPECIFIED:</div> <div>DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH± 1° BEND ± 1° TWO PLACE DECIMAL ±.01 THREE PLACE DECIMAL ±.005 SURFACE FINISH = 63 MAX. CORNER BREAKS = .004</div> <div>THIRD ANGLE PROJECTION</div> <div>MATERIAL<div>SEE TABLE</div></div> <div>FINISH<div>SEE TABLE</div></div> <div>FILE NAME: 8828000G001-055T</div>		NAME		DATE		<div>DELTA ELECTRONICS MFG CORP.</div> <div>BEVERLY, MA 01915</div> <div>www.deltarf.com / Ph: 978-927-1060 / Fax: 978-922-6430</div> <div>TITLE:<div>SMPM STRAIGHT ADAPTER FEMALE TO FEMALE .858 LONG</div></div> <table><tr><td>SIZE</td><td>DWG. NO.</td><td>REV</td></tr><tr><td>B</td><td>8828000G001-055</td><td>-</td></tr></table> <div>CODE ID - 00795</div> <div>WEIGHT: 0.90 g</div> <div>SHEET 1 OF 1</div>				SIZE	DWG. NO.	REV	B	8828000G001-055	-
		SIZE	DWG. NO.	REV											
		B	8828000G001-055	-											
		DRAWN		ADK						3/27/2020					
CHECKED		BJM		3/27/2020											
ENG APPR.		BJM		3/27/2020											
COMMENTS:															

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delta Electronics Mfg Corp:](#)

[8828000G001-055](#)