

LOCTITE ABLESTIK 104

December 2015

PRODUCT DESCRIPTION

LOCTITE ABLESTIK 104 provides the following product characteristics:

Technology	Epoxy
Technology (Part B)	Anhydride
Appearance, Resin (Component A)	Black liquid
Appearance, Hardener (Component B)	White powder
Components	Two component - requires mixing
Mixing Ratio, by weight Component A: Component B	100 : 64
Product Benefits	<ul style="list-style-type: none"> • Excellent chemical resistance • Non-conductive • High shear strength • High temperature resistance • Long pot life
Cure	Heat cure
Application	Assembly
Key Substrates	Metals , Glass, Ceramic and Thermoset plastic
Operating Temperature	-25 to 230°C

LOCTITE ABLESTIK 104 adhesive is designed for applications requiring very high temperature exposures. This adhesive can withstand continuous exposure at temperatures as high as 230°C. It has also been tested to withstand short term exposures up to 280°C.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Part A Properties

Viscosity @ 25 °C, mPa·s (cP)	25,000
Specific Gravity	1.35
Shelf Life @ 25°C, days	183
Flash Point - See SDS	

Part B Properties

Shelf Life @ 25°C, days	183
-------------------------	-----

Mixed Properties

Working Time, 100 g mass @ 25 °C, hours	>12
Density , g/cm ³	1.4

TYPICAL CURING PERFORMANCE

Cure Schedule

- 1 hour @ 200°C
- 2 hours @ 175°C
- 3 hours @ 150°C
- 6 hours @ 120°C

For optimum performance, follow the initial cure with a post cure of 2 to 4 hours at the highest expected use temperature.

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Hardness, Shore D	90
Coefficient of Thermal Expansion TMA, ppm/°C	60
Glass Transition Temperature DSC/TMA, °C	>225

Electrical Properties

Volume Resistivity @ 25°C, ohm-cm	10 ¹⁵
Dielectric Strength, kV/mm	15.7

Outgassing Properties

Outgassing , per NASA Reference Publication 1124, %:
sample cured 6 hours @ 120°C

TML	0.52
CVCM	0.08

Chemical Resistance

Typical Solvent and Chemical Resistance % Weight Change
After 7days Immersion @ 24°C

Chemical	% Weight Change	Chemical	% Weight Change
30% H2so4	+ 0.19	10% NaCl	+ 0.21
3% H2so4	+ 0.26	5% Phenol	+ 0.23
10% NaOH	+ 0.11	Distilled H2O	+ 0.20
1% NaOH	+ 0.22	10% Hno3	+ 0.23
95% c2h5oh	+ 0.7	10% HCl	+ 0.22
50% c2h5oh	+ 0.18	5% ch2cooh	+ 0.24
Acetone	+ 0.06	10% nh4oh	+ 0.76
Ethyl Acetate	+ 0.00	2% Na2CO3	+ 0.22
CCl4	+ 0.04	3% h2o2	+ 0.23
Toluene	+ 0.04	10% Citric Acid	+ 0.22
Heptane	+ 0.02	Oleic Acid	+ 0.09
JP-4	+ 0	JP-5	0

TYPICAL PERFORMANCE OF CURED MATERIAL**Shear Strength**

Tensile Lap Shear Strength :

Aluminum to aluminum:

Tested @ 25 °C	N/mm ²	12.4
	(psi)	(1,800)
Tested @ 150 °C	N/mm ²	11.7
	(psi)	(1,700)
Tested @ 230 °C	N/mm ²	9.7
	(psi)	(1,400)

GENERAL INFORMATION

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

DIRECTIONS FOR USE

1. Complete cleaning of the substrates should be performed to remove contamination such as oxide layers, dust, moisture, salt and oils which can cause poor adhesion or corrosion in a bonded part.
2. Accurately weigh resin and hardener into a clean container in the recommended ratio. Weighing apparatus having an accuracy in proportion to the amounts being weighed should be used.
3. Blend components by hand, using a kneading motion, for 2 to 3 minutes and scrape the bottom and sides of the mixing container frequently to produce a uniform mixture.
4. If possible, power mix for an additional 2 to 3 minutes. Avoid high mixing speeds. This can entrap excessive amounts of air. It can also cause overheating of the mixture, resulting in reduced working life.
5. Apply adhesive to all surfaces to be bonded and join together.
6. In most applications only contact pressure is required.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Storage

Store in original, tightly covered containers in clean, dry areas. Storage information may be indicated on the product container labeling.

Optimal Storage : 25 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions
 $(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N} \cdot \text{m} \times 8.851 = \text{lb} \cdot \text{in}$
 $\text{N} \cdot \text{m} \times 0.738 = \text{lb} \cdot \text{ft}$
 $\text{N} \cdot \text{mm} \times 0.142 = \text{oz} \cdot \text{in}$
 $\text{mPa} \cdot \text{s} = \text{cP}$
Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1187944](#)