

Resistive Termination (Plug Type)




Figure 1




Figure 2

(Safety-wire holes in coupling nut)

Resistor	Fig.	Dimensions			Features	Plating		Delta P/N
		A	B	C		Body	Contact	
51Ω ±5%, 1/2 Watt	1	1.25	3.50	.144	Bead chain	Nickel	Gold (C)	1231-000-N000
51Ω ±5%, 1/2 Watt	1	1.25	—	—	No chain	Nickel	Gold (C)	1231-000-N00A
75Ω ±1%, 1/2 Watt	2	1.25	3.50	.144	Bead chain	Nickel	Gold (C)	1231-000-N000-5
75Ω ±1%, 1/2 Watt	1	1.25	—	—	No chain	Nickel	Gold (C)	1231-000-N00A-2

Dust Caps




Figure 1





Figure 2

See page 198 for MIL-PRF-39012 QPL versions.

Figure	Dimensions			Features	Plating		Delta P/N
	A	B	C		Body	Contact	
1	.53	2.25	.144	Bead chain	Nickel	—	1232-000-N000
1	.37	—	—	No chain	Nickel	—	1232-000-N00A
1	.69	2.25	.144	Bead chain / shorting type	Nickel	Gold (C)	1232-000-N00C
2	.58	3.50	.144	Bead chain	Nickel	—	1233-000-N000-2
2	.58	—	—	No chain	Nickel	—	1233-000-N00A
2	.69	2.50	.144	Bead chain / shorting type	Nickel	Gold (C)	1233-000-N00C

Dummy Receptacle



Dimensions		Mounting Figure	Plating		Delta P/N
A	B		Body	Contact	
.715	.080	09	Nickel	—	1263-000-N090

(C) in contact plating column indicates captive contact. • See page 6 for alternate body plating information.
See page 203 for mounting dimensions. • Caps and terminations are available with other chain styles and/or resistances.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delta Electronics Mfg Corp:](#)

[1232000N000-000](#)