



SPECIFICATIONS


1. CASE:
22 GA. (.030) CRS, TIN PLATED
2. RATED CURRENT:
1A
3. RATED VOLTAGE:
250VAC, 50/60Hz
125VAC, 50-400Hz
4. TEST VOLTAGE:
LINE TO LINE: 1.2KVDC
LINE TO GROUND: 2.2KVDC
5. LEAKAGE CURRENT:
1.8mA @ 250VAC, 50Hz
6. WEIGHT: 0.61LB



INSERTION LOSS (50 Ω TYPICAL)

	.02 MHz	.05 MHz	.15 MHz	1.5 MHz	5.0 MHz	50 MHz
L/L	20 db	35 db	60 db	65 db	65 db	60 db
L/G	35 db	60 db	65 db	65 db	65 db	60 db

SCHEMATIC



REVISION			
LTR	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06-05-02	LE
B	ADD WGT	07-09-10	LE

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ±.030 ± .XXX ±.010	CONTRACT NO.		FILTER CONCEPTS INC.	
	APPROVALS	DATE		
MATERIAL	DRAWN	GIANG TRINH	06-03-02	APPLICATION DRAWING A2T1 FILTER
	CHECKED	DANNIEL VUONG	06-05-02	
FINISH	SIZE	CODE IDENT NO.	DRAWING NO.	7279
NEXT ASSY	B			
USED ON	SCALE	1/1	SHEET	1 OF 1
APPLICATION				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Astrodyne TDI:](#)

[A2T1](#)