

LOCTITE STYCAST ES 4412

June 2016

PRODUCT DESCRIPTION

LOCTITE STYCAST ES 4412 provides the following product characteristics:

Technology	Epoxy
Appearance - Part A	Black
Appearance - Part B	Tan
Appearance (cured)	Black
Components	Two component - requires mixing
Mix Ratio by weight: Part A: Part B	100 : 87
Mix Ratio by volume: Part A: Part B	100 : 100
Product Benefits	<ul style="list-style-type: none"> • Excellent handling properties • Low cost • Flexible • Low exotherm • Good thermal shock resistance • Low viscosity
Cure	Room temperature cure
Application	Potting and Encapsulating

LOCTITE STYCAST ES 4412 two-component casting system formulated for impregnating applications with small tolerances encapsulation of various components and modules. This low cost, flexible system is filled with a non-abrasive filler for machine metering/dispensing.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Part A Properties

Density, @ 25 °C, g/cm ³	1.82
Viscosity, Brookfield - RVF, 25 °C, mPa·s (cP): Spindle 6, speed 2 rpm	14,000
Filler Content, %	50

Part B Properties

Density, @ 25 °C, g/cm ³	1.64
Viscosity, Brookfield - RVF, 25 °C, mPa·s (cP): Spindle 3, speed 10 rpm	3,500
Filler Content, %	55

Mixed Properties

Viscosity, Brookfield - RVF, 25 °C, mPa·s (cP): Spindle 4, speed 10 rpm	10,000
Filler Content, %	52
Peak Exotherm Temperature, °C: 200 g mass	42
Pot Life @ 25 °C, minutes: 200 g mass	60
500 g mass	58
1,000 g mass	47

TYPICAL CURING PERFORMANCE

Recommended Curing Conditions

24 hours @ 25 °C

Alternate Cure Schedule

3 hours @ 60 °C

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Coefficient of Linear Thermal Expansion, ppm/°C:	
Below Tg	74
Above Tg	180
Glass Transition Temperature, °C	36
Tensile Strength	N/mm ² 9.6 (psi) (1,400)
Compressive Strength	N/mm ² 96.5 (psi) (14,000)
Linear Shrinkage, %	0.007
Hardness, Shore D	75
Elongation, %	45
Specific Gravity	1.79
Thermal Conductivity, W/(m·K)	0.293
Izod Impact Strength, ft-lb/in. of notch	0.3
Moisture Absorption, 24 hrs immersion, %	1.1

Electrical Properties

Dielectric Strength, volts/mil	1,100
Dielectric Constant / Dissipation Factor:	
@ 25 °C:	
@ 100Hz	5.7/0.12
@ 1KHz	4.9/0.007
@ 10KHz	4.4/0.063
@ 105 °C:	
@ 100Hz	20/4.36
@ 1KHz	11.8/0.974
@ 10KHz	8.6/0.104
Volume Resistivity, ohm-cm:	
@ 25 °C	2×10 ¹³
@ 105 °C	4×10 ⁹
Surface Resistivity, ohms :	
@ 25 °C	1×10 ¹⁴
@ 105 °C	2×10 ¹¹

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

Directions for use

1. The standard mix ratio of LOCTITE STYCAST ES 4412 is 100 parts A to 100 parts B by volume. By decreasing the amount of hardener to 90 parts Part B by volume, maximum rigidity and hardness will be obtained. By increasing the amount of hardener to 110 parts Part B by volume, flexibility will be increased. Other property variations may also be observed. No mix ratio beyond these two extremes should be used.
2. LOCTITE STYCAST ES 4412 will settle upon storage, especially at temperatures exceeding 27 °C. Refrigerated storage will minimize filler settling. Each container must be thoroughly mixed before combining Part A and Part B. For ease of mixing, store containers upside down. After warming to room temperature, approximately 10 minutes on a standard paint shaker will normally ensure complete dispersion of the filler.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 8°C to 28°C. Storage below 8°C or greater than 28°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N} \cdot \text{m} \times 8.851 = \text{lb} \cdot \text{in}$
 $\text{N} \cdot \text{m} \times 0.738 = \text{lb} \cdot \text{ft}$
 $\text{N} \cdot \text{mm} \times 0.142 = \text{oz} \cdot \text{in}$
 $\text{mPa} \cdot \text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[427431](#) [427432](#) [2260102](#) [2260104](#)