

LOCTITE STYCAST 4350

June 2019

PRODUCT DESCRIPTION

LOCTITE STYCAST 4350 provides the following product characteristics:

Technology	Silicone
Appearance (Resin)	Red liquid
Appearance (Catalyst)	Clear liquid
Product Benefits	<ul style="list-style-type: none"> • Two component • Thermally conductive • Room temperature cure capability • Temperature resistant • Readily pourable
Mix Ratio by weight - Material:Catalyst	100 / 0.1 to 0.4
Cure	Room temperature or Heat cure
Application	Potting or Encapsulation
Operating Temperature	-65 to +260 °C

LOCTITE STYCAST 4350 RTV condensation cure, silicone rubber potting compound is designed for potting and encapsulation of components that require dissipation of heat and the high temperature and low stress properties of a silicone compound. It cures to form a flexible, thermally conductive material having excellent electrical properties and high temperature resistance.

LOCTITE STYCAST 4350 can be used with LOCTITE CAT 50-2.

TYPICAL UNCURED PROPERTIES AS MIXED

LOCTITE STYCAST 4350

Brookfield Viscosity mPa·s (cP)	23,500
Density, g/cm ³	2.1
Flash Point - See SDS	

LOCTITE CAT 50-2

Specific Gravity @ 25°C	1.1
Flash Point - See SDS	

TYPICAL UNCURED PROPERTIES AS MIXED

LOCTITE STYCAST 4350 LOCTITE CAT 50-2 (LOCTITE CAT 50-2 AMB)

Brookfield Viscosity mPa·s (cP)	23,500
Density, g/cm ³	2.1
Work Life @ 25 °C, 100 gram mass, minutes	60
Shelf Life @ 25°C (from date of manufacture), days	152
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE AS MIXED

Cure Schedule (As Mixed)

LOCTITE STYCAST 4350 with LOCTITE CAT 50-2 (LOCTITE CAT 50-2 AMB):

- 16 to 24 hours @ 25°C
- 2 to 4 hours @ 65°C

For optimum performance above 125°C is anticipated, a post cure schedule of 1-2 hours at 25-30°C increments up to the highest expected use temperature is recommended to properly condition the silicone rubber.

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL AS MIXED

LOCTITE STYCAST 4350 with LOCTITE CAT 50-2 (LOCTITE CAT 50-2 AMB)

Physical Properties

Hardness, Shore A	75
Glass Transition Temperature, °C	-55
Coefficient of Thermal Expansion :	
Below Tg, ppm/°C	118
Above Tg, ppm/°C	196
Tear Resistance, lbs/inch	29
Tensile Modulus	N/mm ² 3.04 (psi) (440)
Elongation, %	133
Thermal Conductivity, W/(m-K)	0.95

Electrical Properties

Volume Resistivity @ 25°C, ohms-cm	2.3×10 ¹⁴
Dielectric Strength, volts/mil	619
Dielectric Constant / Dissipation Factor @ 1 MHz	4.9 / 0.0014

TYPICAL PERFORMANCE OF CURED MATERIAL AS MIXED

LOCTITE STYCAST 4350 with LOCTITE CAT 50-2 (LOCTITE CAT 50-2 AMB)

Miscellaneous

Tensile Strength	N/mm ² 3.5 (psi) (508)
------------------	--------------------------------------

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

DIRECTIONS FOR USE

1. Complete cleaning of the components and substrates should be performed to remove contamination such as dust, moisture, salt and oils which can cause electrical failure, poor adhesion or corrosion in an embedded part.
2. This RTV silicone product is based on condensation cure chemistry and will cure in contact with most materials without cure inhibition.
3. This product is not recommended for use in closed molds or sealed molds which could prevent its exposure to moisture or the escape of reaction by-products required to complete the cure.
4. Catalysts used to cure this product may cause corrosion of

copper and other sensitive metals.

5. Some filler settling is common during shipping and storage. For this reason, it is recommended that the contents of the shipping container be thoroughly mixed prior to use.
6. Power mixing is preferred to ensure a homogeneous product.
7. Accurately weigh the liquid RTV silicone and catalyst into a clean container in the recommended ratio.
8. To facilitate the addition of catalyst, the use of a medicine dropper which has been previously calibrated to determine the number of drops per gram is recommended.
9. Working life and cure time are shortened as the amount of catalyst is increased.
10. Low catalyst concentrations are recommended for applications requiring thick sections or use at temperatures in excess of 125 °C.
11. Blend components by hand, using a kneading motion, for 2 to 3 minutes. Scrape the bottom and sides of the mixing container frequently to produce a uniform mixture.
12. Scrape the bottom and sides of the mixing container frequently to produce a uniform mixture.
13. If possible, power mix for an additional 2 to 3 minutes. Avoid high mixing speeds. This can entrap excessive amounts of air. It can also cause overheating of the mixture, resulting in reduced working life.
14. To ensure a void-free embedment, vacuum deairing or degassing should be performed to remove any entrapped air introduced during the mixing operation.
15. Pump-down or pull vacuum on the mixture to achieve an ultimate vacuum or absolute pressure of 1 to 5 torr or mm Hg. The foam will rise several times in the liquid height and then subside.
16. Continue vacuum deairing until most of the bubbling has ceased. This usually takes 3 to 10 minutes.
17. In general, silicone materials exhibit outstanding release properties and will not adhere to most substrates.
18. If adhesion is required, apply a thin, uniform coating of LOCTITE STYCAST S 11NC PRIMER to the desired clean, dry substrates. Allow the LOCTITE STYCAST S 11NC PRIMER to dry for 30-60 minutes at room temperature before applying this silicone material.
19. Pour mixture into cavity or mold.
20. Further vacuum deairing in the mold may be required for critical applications.

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage : 25 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Conversions

(°C x 1.8) + 32 = °F
 kV/mm x 25.4 = V/mil
 mm / 25.4 = inches
 N x 0.225 = lb/F
 N/mm x 5.71 = lb/in
 psi x 145 = N/mm²
 MPa = N/mm²
 N·m x 8.851 = lb·in
 N·m x 0.738 = lb·ft
 N·mm x 0.142 = oz·in
 mPa·s = cP

Disclaimer

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 0.3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[2058834](#)