

LOCTITE STYCAST S 11NC PRIMER

April 2018

PRODUCT DESCRIPTION

LOCTITE STYCAST S 11NC PRIMER provides the following product characteristics:

Technology	Silicone
Appearance	Colorless liquid
Cure	Air
Product Benefits	<ul style="list-style-type: none"> Low viscosity
Application	Encapsulation, Potting

LOCTITE STYCAST S 11NC PRIMER is a low viscosity primer used for enhancing the adhesion of room temperature vulcanizing silicone resins. It is an effective primer for many RTV silicones that are subjected to temperatures as high as 200 to 250°C. This material is supplied as a diluted solution of a moisture reactive material in an anorganic solvent.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Density, g/cm ³	0.8 to 0.84
Shelf Life @ 18 to 25°C (from date of manufacture), days	360
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE

Drying Conditions

Recommended Drying Time, minutes	60 to 90
----------------------------------	----------

Non-Volatiles Contents

Non-VOC, %	3 to 7
------------	--------

The above drying profile is a guideline recommendation. Conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer drying equipment.

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

DIRECTIONS FOR USE

- Surfaces to be printed should be cleaned to remove any oil, grease, scale, mold release or other foreign material.
- Thoroughly clean and degrease the surface with a suitable hydrocarbon solvent such as 1.1.1-trichloroethane. Handling precautions appropriate for the solvent selected should be observed. All solvents should be considered to be toxic and harmful. Adequate ventilation must be provided and precautions taken against exposure of flammable solvents to heat, sparks and open flames.
- Allow sufficient time and temperature for the surface to be completely dry of any cleaning agent.
- Brush or spray a thin coat of LOCTITE STYCAST S 11NC

PRIMER onto surfaces where required. Generally, a thin film or primer will give the best adhesion.

- Typically, LOCTITE STYCAST S 11NC PRIMER should be allowed to dry for at least 60 to 90 minutes. The primer coat should be solvent-free before application of the desired STYCAST product. At lower than normal temperatures and humidity, longer drying times will be required. The following chart will serve as a guide, but the optimum drying time for a specific surface is best determined by experimentation.

Relative Humidity (%)	Suggested Drying Time (h)
>70	1
60	1.5
50	2
40	3
30	5
>20	>7

- If the printed surface is kept clean and stored in an area free from airborne contaminants, RTV silicones can usually be applied at any time up to one week after using LOCTITE STYCAST S 11NC PRIMER.

STORAGE

Storage in cool, clean and dry areas is recommended.

LOCTITE STYCAST S 11NC PRIMER is water sensitive. The container should be kept tightly sealed when not in use. Repeated opening and closing of the container, which exposes the contents to moisture should be avoided.

Prolonged moisture exposure will be indicated by a milky appearance. When this occurs, the effectiveness of the primer will be reduced or destroyed.

Optimal Storage : 18 to 25 °C

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1189914](#)