

LOCTITE ECCOBOND UF 3811

August 2019

PRODUCT DESCRIPTION

LOCTITE ECCOBOND UF 3811 provides the following product characteristics:

Technology	Epoxy
Appearance	Black liquid
Cure	Heat cure
Product Benefits	<ul style="list-style-type: none"> • One component • Room temperature flow capability • Halogen free • Reworkable • Good thermal cycling reliability • Stable electrical performance under standard Surface Insulation Resistance (SIR)
Application	Underfill, Encapsulation
Typical Package Application	Chip scale packages and BGA

LOCTITE ECCOBOND UF 3811 reworkable epoxy underfill is designed for CSP and BGA applications. This low viscosity material is formulated to flow at room temperature with no additional preheating required. It cures quickly at moderate temperatures to minimize stress to other components. When cured, this material has a high glass transition temperature while maintaining flexibility in order to protect solder joints during thermal cycling and drop testing.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Physica CP50-1, 25 °C, mPa·s (cP):	
Speed 20 rpm	354
Specific Gravity	1.16
Pot Life @ 25°C, days	3
Shelf Life @ -20°C, days	365

Flash Point - See SDS

TYPICAL CURING PERFORMANCE

Cure Schedule

60 minutes @ 100°C
30 minutes @ 110°C
10 minutes @ 130°C
7 minutes @ 150°C

The above cure profile is a guideline recommendation. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Coefficient of Thermal Expansion, , TMA:	
Below Tg, ppm/°C	61
Above Tg, ppm/°C	190
Glass Transition Temperature (Tg) by TMA, °C	124
Storage Modulus, DMA, 3-point bending @ 25°C	N/mm ² 2,445 (MPa) (2,445) (psi) (354,617)
Thermal Conductivity, W/(m-K)	0.23

Electrical Properties

Surface Insulation Resistance, after 168 hours, 1×10 ¹⁰ 60°C/90% RH, ohms
--

TYPICAL ENVIRONMENTAL RESISTANCE

Outgassing Properties

Outgassing, NASA Outgassing:	
TML, %	0.45
CVCM, %	0.04
WVR, %	0.31

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage : -20 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb/F}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 0.5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1824593](#) [1911260](#) [2063673](#)