

LOCTITE® ECCOBOND 3707

January 2024

Product description

LOCTITE® ECCOBOND 3707 provides the following product characteristics:

Technology	Epoxy
Appearance	Black liquid
Filler weight, wt%	60
Cure	Heat cured
Typical package application	Flip Chip
Key substrates	PCB
Product benefits	<ul style="list-style-type: none">• One component• Halogen free• High Tg• Snap curable• Fast flow• Easy rework• High fracture toughness

LOCTITE® ECCOBOND 3707 UV curable edgebond is designed for bonding various types of electronic components on a PCB.

Typical properties of uncured material

Viscosity, Brookfield CP52, 25 °C, mPa·s (cP): Speed 20 rpm	9,595
Pot life @ 25°C, days	<7
Shelf Life - Refer to package label	
Flash point - see SDS	

Typical curing performance

Recommended UV cure condition

- >3.000 mJ or
 - >30 seconds @ 100 mW/cm²
- Cure depth, mm:
- MPHL (UVALoc1000) at 100 mW/cm², for 30 seconds ≥10

Oven cure

2 minute @ 130°C

Minimum intensity of 100 mW/cm² is recommended for the UV lamp. Use suggested cure schedules as general guidelines; other cure schedules may yield satisfactory results.

The above cure profile is a guideline recommendation. These conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

Typical properties of cured material

Specimen was prepared by thermal cure only

Physical properties

Coefficient of thermal expansion, ppm/°C:	
Below Tg	52
Above Tg	151
Glass transition temperature, Tg by TMA, °C	53
Storage modulus, GPa	4.4

General information

For safe handling information on this product, consult the Material Safety Data Sheet (MSDS).

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on the specifications of this product.

Removal procedure

1. Heat the cornerbond to approximately 240°C using a hot air nozzle on standard BGA rework equipment.
2. Component can be twisted and removed.
3. Clean and remove residue using a tacky flux or liquid flux and a solder removal vacuum tool.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product package labeling.

Optimal Storage: 2°C to 8°C. Storage below 2°C or greater than 8°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel representative.

Conversions

(°C x 1.8) + 32 = °F
kV/mm x 25.4 = V/mil
mm / 25.4 = inches
µm / 25.4 = mil
N x 0.225 = lb
N/mm x 5.71 = lb/in
N/mm² x 145 = psi
MPa x 145 = psi
N·m x 8.851 = lb·in
N·m x 0.738 = lb·ft
N·mm x 0.142 = oz·in
mPa·s = cP

Additional information

Disclaimer

The information provided in this Technical data sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical data sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[2892430](#) [2813360](#)